






RECOMMENDED LAND PATTERN DIMENSION OF PCB
(RECOMMENDED METAL MASK THICKNESS: 0.15mm)





- NOTES
- 8 HATCHED PARTS: GROUND CIRCUIT.
 - SMT LEAD-COPLANARITY: 0.1 MAX.
 - THIS PRODUCT HAS NO POLARITY TO PATTERN FOR MOUNTING.
 - MAKE SURE WIDTH OF PATTERN IS WITHIN THAT OF LAND, OR LEAD MAY TOUCH PATTERN. (THIS APPLIES TO HATCHED AREA.)
 - DO NOT MOUNT OTHER DEVICES ONTO AREA, OR MATING PAIR CANNOT BE MATED.
 - THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

SIGNAL PORTION CROSS SECTION(10:1)



GROUND PORTION CROSS SECTION(10:1)



3, 4		PHOSPHOR BRONZE	TIN PLATING		2	COPPER ALLOY	CONTACT AREA : GOLD 0.1#m min.					
1		LCP	BEIGE UL94V-0				LEAD AREA : GOLD 0.05#m min.					
							UNDER PLATING : NICKEL 1#m min.					
NO.		MATERIAL		FINISH , REMARKS		NO.	MATERIAL		FINISH , REMARKS			
UNITS mm				SCALE 5 : 1			COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED : HS. OKAWA		11.03.26		DRAWING NO. EDC3-152598-25						
		CHECED : HT. YAMAGUCHI		11.03.26		PART NO. FX11A-80P/8-SV(71)						
		DESIGNED : SY. KAMIGA		11.03.26		CODE NO. CL573-0503-2-71						
		DRAWN : HK. SUNADORI		11.03.26								
												