



1	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	1	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE

MATED (2:1)




PANEL SIZE FIGURE (2:1)



PART No.	CODE No.	A	B	C	D	E	F
DF11- 4DEP-2A	CL543-0698-1-00	11.0	9.2	2.0	6.0	9.4	6.3
DF11- 6DEP-2A	CL543-0699-4-00	13.0	11.2	4.0	8.0	11.4	8.3
DF11- 8DEP-2A	CL543-0700-1-00	15.0	13.2	6.0	10.0	13.4	10.3
DF11- 10DEP-2A	CL543-0701-4-00	17.0	15.2	8.0	12.0	15.4	12.3
DF11- 12DEP-2A	CL543-0702-7-00	19.0	17.2	10.0	14.0	17.4	14.3
DF11- 14DEP-2A	CL543-0703-0-00	21.0	19.2	12.0	16.0	19.4	16.3
DF11- 16DEP-2A	CL543-0704-2-00	23.0	21.2	14.0	18.0	21.4	18.3
DF11- 18DEP-2A	CL543-0705-5-00	25.0	23.2	16.0	20.0	23.4	20.3
DF11- 20DEP-2A	CL543-0706-8-00	27.0	25.2	18.0	22.0	25.4	22.3
DF11- 22DEP-2A	CL543-0707-6-00	29.0	27.2	20.0	24.0	27.4	24.3
DF11- 24DEP-2A	CL543-0708-3-00	31.0	29.2	22.0	26.0	29.4	26.3
DF11- 26DEP-2A	CL543-0709-6-00	33.0	31.2	24.0	28.0	31.4	28.3
DF11- 28DEP-2A	CL543-0710-5-00	35.0	33.2	26.0	30.0	33.4	30.3
DF11- 30DEP-2A	CL543-0711-8-00	37.0	35.2	28.0	32.0	35.4	32.3
DF11- 32DEP-2A	CL543-0712-0-00	39.0	37.2	30.0	34.0	37.4	34.3

NOTES:
 1 IN COMBINATION WITH DF11-*DS-2C, IT IS 16.9 mm.
 2 THE THICKNESS OF A CONFORMITY PANEL IS 1 mm TO 1.6 mm.
 (SHAKINESS OF SOME ARISES EXCEPT 1.2 mm OR 1.6 mm.)
 3 TERMINAL NO.1 TO THE SOCKET WHICH MATED IS EXPRESSED.
 KEEP IN MIND THAT THE CIRCUIT AT THE TIME OF CARRYING OUT SOCKET MATED BECOMES
 BOTH SIDES WITH TERMINAL NO.1 OF A SOCKET 1,
 AND CONNECTION OF A SOCKET 2 OF TERMINAL NO.2.
 4 THE POSITION OF HRS MARK AND CAV. MARK ALSO HAS THE CASE OF THE FOLLOWING FIGURE.



1	POLYAMIDE	UL94V-0, BLACK	2	BRASS	SURFACE: TIN PLATED 1 μm min UNDER PLATING: NICKEL PLATED 0.5 μm min		
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS		
CODE NO. (OLD)			DRAWN		DESIGNED	CHECKED	APPROVED
			A. Miura		R. Ishii	H. Uemura	J. Gia
			'06.10.03		'06.10.03	'06.10.03	'06.10.03
SCALE 5 : 1 UNITS mm		DRAWING NO. EDC3-313906-00			PART NO. DF11-*DEP-2A		
					CODE NO. CL543-		

HRS HIROSE ELECTRIC CO., LTD