



Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

TO

A
B
C
D
E
F



COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△				..	△				..
△				..	△				..
△				..	△				..

HR'S DRAWING FOR REFERENCE

NOTES1.PER REEL:10000 CONTACTS.
2.APPLICABLE CABLE
CABLE SIZE:30AWG(7/0.10) AND 32AWG(7/0.08)
OUTER DIAMETER:φ0.5 TO 0.6mm.

1		PHOSPHOR BRONZE		CONTACT AREA UNDER PLATED:NICKEL PLATED 0.5μm min. SURFACE PLATED:GOLD PLATED 0.2μm min BARREL AREA UNDER PLATED:NICKEL PLATED 0.5μm min SURFACE PLATED:TIN PLATED 1μm min OTHERS:NICKEL PLATED 0.5μm min			
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS	
CODE NO.(OLD)		DRAWN		DESIGNED		CHECKED	
		A.MIYAZAKI		A.MIYAZAKI		H. Umehara	
		06.05.18		06.05.18		06.05.19	
SCALE 20:1		DRAWING NO. EDC3-164752-01		PART NO. DF19A-3032SCFA		APPROVED T. Ama	
UNITS mm		HRS HIROSE ELECTRIC CO.,LTD.		CODE NO. CL685-0046-0		RELEASED 1/1	