



Dec.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Note 1. Per pack : 100 pieces.
2. UL (File No.E52653)
C-UL (File No.E52653)
TÜV (Certificate No.R50244085) authorization article.




			1		PBT		BLACK, UL94V-0				
NO.	MATERIAL		FINISH . REMARKS			NO.	MATERIAL		FINISH . REMARKS		
UNITS mm		SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE
 HIROSE ELECTRIC CO., LTD.			APPROVED : KI. AKIYAMA		14. 06. 06	DRAWING NO.		EDC3-344824-01			
			CHECKED : TS. FUKUSHIMA		14. 06. 06	PART NO.		DF60-5EP-10. 16C			
			DESIGNED : TS. KUMAZAWA		14. 06. 06	CODE NO.		CL680-3028-3-00			
			DRAWN : TS. KUMAZAWA		14. 06. 06					1/2	


Dec.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

DF60 In-Line type recommended panel mounting manual (When nuts uses)


Nut installation process



1. Slide a nut (Size:M3) to nut fix part.




2. Press down the nut until it clicks, then this sound means the nut has inserted into nut holder.




Panel mounting process

1. Insert connector into panel cut out part.



2. Tighten a screw (Size:M3) to fix with panel.
recommended torque : less than 49N · cm



HRS

DRAWING NO.	EDC3-344824-01
PART NO.	DF60-5EP-10.16C
CODE NO.	CL680-3028-3-00