





Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




M3.5X0.6  
 (EFFECTIVE SCREW LENGTH 3 min)




△ 2 PRODUCT - BOARD MOUNTED

RECOMMENDED PC BOARD PATTERN



RECOMMENDED PANEL CUOUT  
 (PANEL THICKNESS : 1.6mm MAX)



NOTES 1 PART No. 7 SHALL BE FINISHED AS TABLE SHOWN BELOW ACCORDING TO PANEL THICKNESS. (WASHER THICKNESS : 0.8)  
 2 This product must be screwed to the board. Please prepare the screws by the customer. <SCREW REQUIREMENTS>  
 NOMINAL DIAMETER: M3.5 x 0.6  
 SCREW LENGTH : 2.4 ± 0.6 + BOARD thickness 't'

PANEL THICKNESS	No. OF WASHER
t=0.7~1.0	2 EACH
t=1.5~1.8	1 EACH

NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
4	ZINC ALLOY DIE CASTING	OVER: NICKEL PLATING 2#m min UNDER: COPPER PLATING 10#m min	7	STEEL	OVER: NICKEL PLATING 2#m min UNDER: COPPER PLATING 3#m min
3	PBT	UL94V-0(BLACK)	6	BRASS	OVER: NICKEL PLATING 2#m min UNDER: COPPER PLATING 1#m min
2	PBT	UL94V-0(BLACK)	5	STEEL	OVER: NICKEL PLATING 1#m min UNDER: COPPER PLATING 5#m min
1	PHOSPHOR BRONZE	CONTACT: GOLD PLATING 0.2#m min DIP GOLD PLATING 0.03#m min UNDER: COPPER PLATING 2#m min			

UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	2	DIS-E-00010989	KG. OKITA	MN. KENJO	20220908

APPROVED	CHECKED	DESIGNED	DRAWN	DRAWING NO.	PART NO.	CODE NO.
HO. MIWA	YH. ENAMI	TU. TANIGUCHI	TU. TANIGUCHI	EDC3-041235-01	DX20A-36S(50)	CL0230-0156-8-50