









Feb.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTE 1 Contact area : Gold plating 0.3μm min
Lead area : Gold plating 0.03μm min
Under : Nickel plating 2μm min
- NOTE 2 This product must be screwed to the board.
Please prepare the screws by the customer.
<SCREW REQUIREMENTS>
NOMINAL DIAMETER: M2.6 x 0.45
SCREW LENGTH : 1.8 ± 0.45 + BOARD thickness 't'

3	PBT	UL94V-0(BLACK)						
2	PBT	UL94V-0(BLACK)		5	STEEL	NICKEL PLATING		
1	PHOSPHOR BRONZE			4	ZINC ALLOY DIE CASTING	NICKEL PLATING		
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS		
UNITS mm		SCALE 2 : 1	 COUNT 4	DESCRIPTION OF REVISIONS DIS-E-00010989		DESIGNED KG. OKITA	CHECKED MN. KENJO	DATE 20220908
 HIROSE ELECTRIC CO., LTD.		APPROVED : HO. MIWA		20050105		DRAWING NO. EDC3-041444-01		
		CHECKED : YH. ENAMI		20050105		PART NO. DX20M-26S(50)		
		DESIGNED : TU. TANIGUCHI		20050105		CODE NO. CL0230-5014-0-50		
		DRAWN : TU. TANIGUCHI		20050105		 		