








RECOMMENDED PC BOARD PATTERN(MOUNTING SIDE)



PANEL CUTOUT (PANEL THICKNESS SHALL BE 1.6mm MAX)



1 PRODUCT - BOARD MOUNTED

- △ NOTES 1 This product must be screwed to the board.
Please prepare the screws by the customer.
<SCREW REQUIREMENTS>
NOMINAL DIAMETER: M2.6 x 0.45
SCREW LENGTH : 1.8 ± 0.45 + BOARD thickness 't'

3	PBT	UL94V-0			
2	PBT	UL94V-0	5	STEEL	NICKEL PLATING
1	PROSPHOR BRONZE	SELECTIVE GOLD PLATING 0.3 μm	4	ZINC ALLOY DIE CASTING	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
UNITS mm	⊙	SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-E-00010989	DESIGNED KG. OKITA
HRS HIROSE ELECTRIC CO., LTD.		APPROVED : HO. MIWA	20050105	DRAWING NO.	EDC3-040855-01
		CHECKED : YH. ENAMI	20050105	PART NO.	DX20M-50S(50)
		DESIGNED : TU. TANIGUCHI	20050105	CODE NO.	CL0230-5016-6-50
		DRAWN : TU. TANIGUCHI	20050105		
					1/1