





NOTE 1 CONTACT CO-PLANARITY TO BE MAX 0.15.
2 TOLERANCES TO BE ± 0.1 UNLESS OTHERWISE SPECIFIED.
3 DEVICE DESIGN SHALL CONSIDER THE STACKED HEIGHT TO BE 14.5mm MAX.
(RECOMMENDED STACKED HEIGHT IS 13.7mm MAX.)
4 CONTACT AREA :GOLD PLATING 0.2 μ m min
LEAD AREA :GOLD PLATING 0.03 μ m min
UNDER :NICKEL PLATING 2 μ m min
1 5 DIP AREA :TIN PLATING 1 μ m min
UNDER :NICKEL PLATING 0.6 μ m min


3	LCP	UL94V-0, Black	7	Pick & Place tape	
2	Phosphor Bronze	4	6	PS	Milky-white
2	Phosphor Bronze	4	5	PS	Milky-white
1	Copper Alloy	4	4	Stainless Steel	5
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

UNITS mm		SCALE 2 : 1		COUNT 1	DESCRIPTION OF REVISIONS DIS-E-00004011	DESIGNED MO. SHIMOYAMA	CHECKED TU. TANIGUCHI	DATE 20210120
 HIROSE ELECTRIC CO., LTD.					APPROVED : MN. KENJO 20200407 CHECKED : TU. TANIGUCHI 20200407 DESIGNED : KIM JAEHYEON 20200407 DRAWN : DS. HIROWATARI 20200407	DRAWING NO. EDC-122485-70-00 PART NO. EX80-100S(70) CODE NO. CL0232-0592-2-70		

5
6
7
8

Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

EX80-100S PACKAGING FIGURE



NOTE 6 QUANTITY PER TRAY TO BE 60 PCS MAX.
ORDERING VOLUME TO BE MADE BY QUANTITY OF CONNECTOR.
7 A TYPE AND B TYPE TRAY PILED UP ONE AFTER ANOTHER.

HRS

DRAWING NO.	EDC-122485-70-00
PART NO.	EX80-100S(70)
CODE NO.	CL0232-0592-2-70

1/2