


Oct.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes
- ① Hand crimping tool, Ref.No. ⑨: HR10A-TC-02 (CL150-0041-2)
 - ① The hole diameter for crimping: $\phi 7$.
 - ② The recommended clamp torque, Ref.No. ⑦: 2 to 2.5 N · m.
 - ③ Across flats hexagon head of Ref.No. ⑧: 1.27
 The recommended clamp torque, Ref.No. ⑧: 0.3 to 0.4 N · m.
 The tip of Ref.No. ⑧ shall be fixed to the concave portion with Ref.No. ⑨ clamped to the cable.
 - ④ Loctite 243, Henkel Japan or equivalent apply to prevent Ref.No. ① and ⑧ from loosening.
 - 5 One example of the rotation of Ref.No. ⑦ to Ref.No. ① is shown.
 - 6 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure. Please confirm before the use. △ CAD change

5	Polyamide	(Black) UL94V-0	10	Chloroprene rubber	(Black)		
4	Brass	Silver plating 2 μ m min.	9	Brass			
3	Brass	Silver plating 2 μ m min.	8	Steel	Nickel plating Hexagon socket set Screw M2.6×0.45×3		
2	Stainless steel		7	Brass	Matte finish nickel plated		
1	Zinc alloy	Matte finish nickel plated	6	Brass	Matte finish nickel plated		
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS

HIROSE ELECTRIC CO., LTD.	UNITS mm		SCALE 2:1	COUNT 5	DESCRIPTION OF REVISIONS DIS-C-00020492	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI	DATE 2025. 07. 31
	APPROVED : MO. SATOH CHECKED : E.J. KUNII DESIGNED : TO. HORII DRAWN : MK. SATO	2007. 03. 08 2007. 03. 08 2007. 03. 08 2007. 03. 08	DRAWING NO. EDC-021371-73-73 PART NO. HR10A-10J-10P (73) CODE NO. CL0110-0412-3-73	1/1				