



Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES 1 APPLICABLE CRIMP CONTACT:
 HR10-PC-212(CL110-0514-3)
 APPLICABLE WIRE:AWG#26 TO #30
 (COVERED WIRE MAX. OUTSIDE DIA.φ1)
 APPLICABLE CONTACT REMOVAL TOOL
 (EXTRACTION TOOL):RP6-SC-TP(CL150-0039-0)
 ② APPLICABLE CRIMPING TOOL OF REF.NO. ⑦:
 HR10A-TC-02(CL150-0041-2)
 THE HOLE DIAMETER FOR CRIMPING:φ7.0
 ③ THE RECOMMENDED CLAMP TORQUE, REF.NO. ⑤
 : 2 TO 2.5 N·m.
 ④ ACROSS FLATS HEXAGON HEAD OF REF.NO. ⑥ : 1.27
 THE RECOMMENDED CLAMP TORQUE,
 REF.NO. ⑥ : 0.3 TO 0.4N·m.
 THE TIP OF REF.NO. ⑥ SHALL BE FIXED TO
 THE CONCAVE PORTION WITH REF.NO. ⑦ CLAMPED
 TO THE CABLE.
 ① ⑤ LOCTITE 263, HENKEL JAPAN OR EQUIVALENT APPLIES
 TO PREVENT REF.NO. ① AND ⑥
 FOR LOOSENING.
 6 ONE EXAMPLE OF THE ROTATION OF REF.NO. ⑤ TO
 REF.NO. ① IS SHOWN.
 7 THE CABLE PULL AND TWISTING STRENGTH AND
 OTHER CHARACTERISTICS MAY DIFFER,
 DEPENDING ON THE CABLE STRUCTURE.
 PLEASE CONFIRM BEFORE THE USE.
 ① 8 THE ASSEMBLY THIS PRODUCT APPLIES TO
 THE MANUAL ETAD-C0354-00.

CONTACT ARRANGEMENTS
 VIEWED FROM THE MATING SIDE



4	STEEL	NICKEL PLATING	8	CHLOROPRENE RUBBER	(BLACK)
3	BRASS	MATTE FINISH NICKEL PLATED	7	BRASS	
2	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0	6	STEEL	NICKEL PLATING M2.6X0.45X3
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	5	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT ① 2	DESCRIPTION OF REVISIONS DIS-C-00017346	DESIGNED HT. ZENBA	CHECKED HY. KOBAYASHI	DATE 20240508
APPROVED :MO. SATOH 20070313 CHECKED :EJ. KUNII 20070312 DESIGNED :TO. HORII 20070309 DRAWN :MK. SATO 20070309				DRAWING NO. EDC4-021261-73 PART NO. HR10A-10P-12PC(73) CODE NO. CL0110-0603-1-73			