


Oct.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

1		2		3		4			
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				
△					△				



NOTES 1 APPLICABLE CRIMP CONTACT:
 HR10-PC-212(CL110-0514-3)
 APPLICABLE WIRE:AWG#26 TO #30
 (COVERED WIRE MAX. OUTSIDE DIA. φ 1)
 APPLICABLE CONTACT REMOVAL TOOL
 (EXTRACTION TOOL):RP8-SC-TP(CL150-0039-0)
 2 APPLICABLE CRIMPING TOOL OF REF.NO. ⑦:
 HR10A-TC-02(CL150-0041-2)
 THE HOLE DIAMETER FOR CRIMPING:φ 7.0
 3 THE RECOMMENDED CLAMP TORQUE,REF.NO. ⑤
 : 2 TO 2.5 N·m.
 4 ACROSS FLATS HEXAGON HEAD OF
 REF.NO. ⑥ : 1.27
 THE RECOMMENDED CLAMP TORQUE,
 REF.NO. ⑥ : 0.3 TO 0.4N·m.
 THE TIP OF REF.NO. ⑥ SHALL BE FIXED TO
 THE CONCAVE PORTION WITH REF.NO. ⑦
 CLAMPED TO THE CABLE.
 5 LOCTITE 242,HENKEL JAPAN OR EQUIVALENT
 IS RECOMMENDED TO PREVENT REF.NO. ①AND ⑥
 FOR LOOSENING.
 6 ONE EXAMPLE OF THE ROTATION OF REF.NO. ⑤ TO
 REF.NO. ① IS SHOWN.
 7 THE CABLE PULL AND TWISTING STRENGTH AND
 OTHER CHARACTERISTICS MAY DIFFER,
 DEPENDING ON THE CABLE STRUCTURE.
 PLEASE CONFIRM BEFORE THE USE.

8	CHLOROPRENE RUBBER	(BLACK)			
7	BRASS				
6	STEEL	NICKEL PLATING M2.6×0.45×3			
5	BRASS	MATTE FINISH NICKEL PLATED			
4	BRASS	MATTE FINISH NICKEL PLATED			
3	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0			
2	STAINLESS STEEL				
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED			

NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
2	STAINLESS STEEL		8	CHLOROPRENE RUBBER	(BLACK)
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	7	BRASS	

CODE NO. (OLD) CL	DRAWN <i>M. Sato</i> 07.03.13	DESIGNED <i>T. Morai</i> 07.03.13	CHECKED <i>E. Yumii</i> 07.03.13	APPROVED <i>M. Sato</i> 07.03.15	RELEASED
DRAWING NO. EDC4-029111-73	PART NO. HR10A-13J-20PC(73)				
SCALE 2 : 1	CODE NO. CL110-0706-4-73				1 1
UNITS mm	HRS HIROSE ELECTRIC CO.,LTD.				

TO
R