


Feb. 1. 2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

1		2			3			4		
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	
△					△					
△					△					
△					△					



- NOTES
- APPLICABLE CRIMP CONTACT: HR12-SC-212 (CL112-0408-9)
APPLICABLE WIRE: AWG#26 TO #30
(COVERED WIRE MAX. OUTSIDE DIA. ϕ 1)
 - APPLICABLE CONTACT REMOVAL TOOL
(EXTRACTION TOOL): HR12-SC-TP (CL150-0050-3)
 - APPLICABLE CRIMPING TOOL OF REF. NO. ⑦:
HR10A-TC-02 (CL150-0041-2)
THE HOLE DIAMETER FOR CRIMPING: ϕ 5.3
 - THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑤:
1.5 TO 2 N·m.
 - ACROSS FLATS HEXAGON HEAD OF REF. NO. ⑥: 1.27
THE RECOMMENDED CLAMP TORQUE,
REF. NO. ⑥: 0.3 TO 0.4N·m.
THE TIP OF REF. NO. ⑥ SHALL BE FIXED TO
THE CONCAVE PORTION WITH REF. NO. ⑦ CLAMPED
TO THE CABLE.
 - LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS
RECOMMENDED TO PREVENT REF. NO. ① AND ⑥
FOR LOOSENING.
 - ONE EXAMPLE OF THE ROTATION OF REF. NO. ⑤ TO
REF. NO. ① IS SHOWN.
 - THE CABLE PULL AND TWISTING STRENGTH AND
OTHER CHARACTERISTICS MAY DIFFER,
DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.

4	BRASS	MATTE FINISH NICKEL PLATED	8	CHLOROPRENE RUBBER (BLACK)	
3	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0	7	BRASS	
2	STAINLESS STEEL		6	STEEL NICKEL PLATING M2.6×0.45×2	
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	5	BRASS MATTE FINISH NICKEL PLATED	
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD) CL		DRAWN <i>M. Kato</i> 07.03.08	DESIGNED <i>J. Hori</i> 07.03.09	CHECKED <i>E. Yumii</i> 07.03.12	APPROVED <i>M. Saito</i> 07.03.13	RELEASED
DRAWING NO. EDC4-021664-73		PART NO. HR10A-7J-6SC(73)				
SCALE 2 : 1		CODE NO. CL110-0512-8-73				1 1
UNITS mm		HRS HIROSE ELECTRIC CO., LTD.				

TO
R