


	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					.	△					.
△						△					.
△						△					.




NOTE 1 APPLICABLE CONTACT: HR12-SC-212

APPLICABLE WIRE: AWG#26~30 (INSULATOR OUTER DIA. OF ϕ 1 OR LESS)

APPLICABLE TO: 100025-001 INSERTS

2 THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑤ : 1.5N · m .

REF. NO. ⑤ FROM LOOSENING.

3	PBT	(BLACK) UL94V-0					
2	STAINLESS STEEL		5	BRASS	NICKEL PLATING		
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	4	PHOSPHOR BRONZE	NICKEL PLATING		
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS		
CODE NO.(OLD) CL			DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
			H.Kishi '05.08.29	H.Kishi '05.08.29	E.Kimura '05.08.30	M.Sato '05.08.30	
F	 	DRAWING NO. EDC4-021660-73	PART NO. HR10A-7R-4SC(73)				
SCALE	2 : 1			CODE NO.			
UNITS	mm			CL 110-0506-5-73			1/1