

1			2			3			4			
COUNT	DESCRIPTION OF REVISIONS		BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS		BY	CHKD	DATE	
△△			.	.	.	△△			.	.	.	
△△			.	.	.	△△			.	.	.	
△△			.	.	.	△△			.	.	.	
A A												
D A DETAIL OF MOUNTING GUIDE D												
D PANEL CUTOUT D												
E												
F												
NOTE 1 APPLICABLE CONTACT : HR10-PC-212 APPLICABLE WIRE : AWG#26~30 ( INSULATOR OUTER DIA. OF Ø 1 OR LESS ) APPLICABLE TOOL,EXTRACTPR : RP6-SC-TP ② THE RECOMMENDED CLAMP TORQUE OF REF.NO.⑤ : 1.5N · m . LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ⑤ FROM LOOSENING.												
3	PBT		(BLACK) UL94V-0			5	BRASS		NICKEL PLATING			
2	STAINLESS STEEL					4	PHOSPHOR BRONZE		NICKEL PLATING			
1	ZINC ALLOY		MATTE FINISH NICKEL PLATED			NO.	MATERIAL		FINISH, REMARKS			
NO.	MATERIAL		FINISH, REMARKS			NO.	MATERIAL		FINISH, REMARKS			
CODE NO. (OLD)				DRAWN		DESIGNED		CHECKED		APPROVED		RELEASED
CL				H.Kishi		H.Kishi		E.Kunii		M.Sato		
				65.08.29		65.08.29		65.08.30		65.08.30		
 SCALE 2 : 1		DRAWING NO.				PART NO.						
		EDC4-025178-73				HR10A-7R-6PC(73)						
 UNITS mm		 HIROSE ELECTRIC CO.,LTD.				CODE NO.						
				CL110-0507-8-73							1/1	