


Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

TO
R

A
B
C
D
E
F

1 2 3 4 5 6 7 8

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△				.	△				.
△				.	△				.
△				.	△				.



NOTE: 1 APPLICABLE CRIMPING CONTACT : HR22-SC-222(CL122-0008-8)
(APPLICABLE WIRE : AWG#24~28, OUTER DIMENSION OF JACKET: φ 1.15MAX)
APPLICABLE CONTACT EXTRACTION TOOL : RP6-SC-TP(CL150-0039-0)
2 ACROSS FLATS OF HEXAGON SOCKET OF REF.NO. ⑩, ⑫: 1.27.
3 THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑧: 2 N·m.
LOCTITE 271, LOCTITE OR EQUIVALENT IS RECOMMENDED TO PREVENT REF.NO. ⑧ FROM LOOSENING.
4 THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑩, ⑫: 0.3 TO 0.4 N·m.
5 ROTATION EXAMPLES OF REF.NO. ① AND ⑧ ARE SHOWN.

6	PHOSPHOR BRONZE	NICKEL PLATING	12	STEEL	NICKEL PLATING M2.6×0.45×3
5	STEEL	ZINC CHROMATED	11	BRASS	
4	BRASS	NICKEL PLATING	10	STEEL	NICKEL PLATING M2.6×0.45×2
3	SIR	(BLACK)	9	NBR	(BLACK)
2	PBT	(BLACK) UL94V-0	8	BRASS	NICKEL PLATING
1	ZINC ALLOY	NICKEL PLATING	7	SIR	(BLACK)
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD)			DRAWN	DESIGNED	CHECKED
			J. Komatsu	J. Komatsu	E. Kunita
			06.03.17	06.03.17	06.03.18
					06.03.20
DRAWING NO.			PART NO.		
EDC3-043648-73			HR22-12TPD-20SC(73)		
UNITS			CODE NO.		
mm			CL122-0010-0-73		
HRS HIROSE ELECTRIC CO., LTD.			1/1		

1 2 3 4 5 6 7 8