

Fig.2 The recommended panel dimension. (t=5.5 (MAX))  
(As viewed from mating side.)





Fig.3 The state applicable connector set up.



Notes 1 Fig.1 shows the state applicable contact assembled applicable crimping contact:HR41-PC-151

2 Applicable crimp contact extraction tool:HR41-TP

3 The recommended tightening torque of Ref. No. ④ to be 5 to 5.5 N·m.

4 Fig.2 shows the recommended panel dimension.

Fig.3 shows the state applicable connector set up.

When connector set up, it in order of Ref.②, panel, Ref.③, Ref.④.

Please check Ref No.② is properly set at the groove of Ref.①.

While mounting the connector, make sure that Ref No.② is not caught.

5 The assembly of this product applies to the manual ETAD-C0288

6 The surface roughness of the cross-hatched part should be applied to the wiring side.

NO.	MATERIAL	FINISH	REMARKS	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
				SCALE	COUNT			
2	Silicone rubber	(Light red)		1:1	1	DIS-C-00019058	TY. SUZUKI	KN. IKEHARA 2025.01.24
1	Polyamide	(Black) UL94V-0				APPROVED : SU. OBARA	2012.06.20	DRAWING NO. EDC-117699-00-00
4	Polyamide	(Black) UL94V-0				CHECKED : HY. KOBAYASHI	2012.06.20	PART NO. HR41-25WBRA-5PC
3	Stainless steel					DESIGNED : TY. SUZUKI	2012.06.20	CODE NO. CL0141-0010-8-00
5						DRAWN : TY. SUZUKI	2012.06.20	

**HRS**  
HIROSE  
ELECTRIC  
CO., LTD.