





- Notes
- Assemble coaxial connectors MRF14-CON(F)(CL313-0709-8), MRF14-CON(MC)(CL313-0716-3), MRF14-CON(M1)(CL313-0710-7) or MRF14-CON(M2)(CL313-0711-0) into holes ($14 \times \phi 2.45$).
 - Don't make an impact in this direction, due to ultrasonic welding.

RoHS COMPLIANT

NON MAGNETIC

2	BERYLLIUM COPPER	NICKEL PLATING			
1	PBT	UL94V-0(WHITE)	3	PBT	UL94V-0(WHITE)
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
UNITS mm		SCALE 2 : 1	COUNT 4	DESCRIPTION OF REVISIONS DIS-D-003435	DESIGNED HA. NISHIMURA
HIROSE ELECTRIC CO., LTD.		APPROVED : MH. YAMANE	12.09.05	DRAWING NO.	EDC3-333791-00
		CHECKED : MH. TSUCHIDA	12.09.04	PART NO.	MRF14-CON(M)-14M
		DESIGNED : TS. KANEKO	12.09.04	CODE NO.	CL313-0706-0-00
		DRAWN : YY. KOBAYASHI	12.09.04		
					14.10.16
					1