

Feb.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.








Fig.1 Reel drawing



- Note:
1. Applicable wire is UL3266 AWG#24-#26.
Insulation diameter $\phi 1.49\text{mm}$ max.
 2. Per reel : 10000 contacts.
 3. Applicable crimping machine and crimping conditions (crimp height etc.) will be specified according to AWG # or wire applied.
 4. Refer to ATAI-E3142 for crimp quality standards.
 5. For details of the packaging method of this product, refer to ETAP-E3151.

1	Copper alloy	Contact area : gold plating min. $0.2\mu\text{m}$ Terminal area : tin plating min. $0.5\mu\text{m}$ Others: nickel plating min. $0.5\mu\text{m}$
NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 10 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-E-00013914	DESIGNED KG. OKITA	CHECKED TU. TANIGUCHI	DATE 20230512
HRS HIROSE ELECTRIC CO., LTD.				APPROVED : AH. KODAMA 20150721	DRAWING NO. EDC-128587-00-00		
				CHECKED : AH. KODAMA 20150721	PART NO. MT50A-2426SCFA		
				DESIGNED : KI. KAGOTANI 20150721	CODE NO. CL0248-0004-8-00		
				DRAWN : KI. KAGOTANI 20150721	1/1		