


Nov.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes 1 Applicable crimp contact:
 Contact No. 1 to 11
 RP13A-SC-222/CL113-0151-0
 (Applicable cable size : awg#24 to #28.
 Cable jacket outer diameter shall be φ1.4mm or less.)
 Contact No. 12, 13
 RP13A-SC-212/CL113-0150-8
 (Applicable cable size : awg#18 to #22.
 Cable jacket outer diameter shall be φ1.9mm or less.)
 2 Applicable cable crimping tool :
 RP13A-TC-01/CL150-0070-0
 3 Extraction tool : RP13A-SC-TP/CL150-0022-8
 4 The tightening torque of Ref No. ⑥ : 0.15 to 0.2 N · m.
 To prevent loosening Ref No. ⑥ , use LOCTITE 243,
 HENKEL JAPAN or equivalent.
 5 Shall be disassembled when delivered.
 6 The cable pull and twisting strength
 and other characteristics may differ,
 depending on the cable structure,
 please confirm before the use.

4	Brass				
3	Polycarbonate	(BLACK) UL94V-0	7	Polyvinylchloride	(BLACK)
2	Polycarbonate	(BLACK) UL94V-0	6	Brass	Black chromete treatment (Trivalent chromium) JIS B 1111 M2X0.4X4
1	Polycarbonate	(BLACK) UL94V-0	5	Steel	Nickel plating
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
		2 : 1	2	DIS-C-00009777	TY. SUZUKI	HY. KOBAYASHI	20220209
HRS HIROSE ELECTRIC CO., LTD. APPROVED : MR. YOSHIDA 20050105 CHECKED : MO. SATOH 20050105 DESIGNED : YH. YAMADA 20050105 DRAWN : YH. YAMADA 20050105				DRAWING NO. EDC4-009810-71 PART NO. RP13A-12PA-13SC(71) CODE NO. CL0113-0182-4-71			