


Feb.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes
- ① 1 Applicable crimp contact:  
 RP19-SC-222/CL113-0266-2 (Applicable cable size : AWG#24 to #28.  
 Cable jacket outer diameter shall be  $\phi 1.15\text{mm}$  or less.)
  - ① 2 Applicable cable crimping tool : RP13A-TC-01/CL150-0070-0
  - 3 Extraction tool : RP6-SC-TP/CL150-0039-0
  - ① ④ The tightening torque of Ref No. ⑥ : 0.15 to 0.2 N·m.  
 To prevent loosening Ref No. ⑥ , use LOCTITE 243, HENKEL JAPAN or equivalent.
  - 5 Shall be disassembled when delivered.
  - 6 The cable pull and twisting strength and other characteristics may differ,  
 depending on the cable structure, please confirm before the use.

4	Brass			7	Polyvinylchloride	(Black)
3	Polycarbonate	(Black)	UL94V-0	6	Brass	Black chromete treatment (Trivalent chromium) JIS B 1111 M2X0.4X4
2	Polycarbonate	(Black)	UL94V-0	5	Steel	Nickel plating
1	Polycarbonate	(Black)	UL94V-0			
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT ① 4	DESCRIPTION OF REVISIONS DIS-C-00009810	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI	DATE 20220215
-------------	--	----------------	--------------	--	------------------------	--------------------------	------------------

HIROSE ELECTRIC CO., LTD.	APPROVED :EJ. KUNII	20160517	DRAWING NO.	EDC-021588-71-00
	CHECKED :EJ. KUNII	20160517	PART NO.	RP13A-12PG-20SC(71)
	DESIGNED :MM. ISHII	20160517	CODE NO.	CL0113-0210-8-71
	DRAWN :MM. ISHII	20160517		① 1 / 1