




- Notes
- Applicable crimp contact:
RP19-SC-222/CL113-0266-2
(Applicable cable size : awg#24 to #28.
Cable jacket outer diameter shall be φ1.15mm or less.)
 - Applicable cable crimping tool : RP13A-TC-02/CL150-0071-3
 - Extraction tool : RP6-SC-TP/CL150-0039-0
 - The tightening torque of Ref. No. ⑥ : 0.15 to 0.2 N·m.
To prevent loosening Ref. No. ⑥ , use LOCTITE 243,
HENKEL JAPAN or equivalent.
 - Shall be disassembled when delivered.
 - The cable pull and twisting strength
and other characteristics may differ,
depending on the cable structure,
please confirm before the use.

4	Brass								
3	Polycarbonate	(Black) UL94V-0	7	Polyvinylchloride	(Black) UL94V-0				
2	Polycarbonate	(Black) UL94V-0	6	Brass	Black chromete treatment (Trivalent chromium) JIS B 1111 M2X0.4X4				
1	Polycarbonate	(Black) UL94V-0	5	Steel	Nickel plating				
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS			
UNITS mm		SCALE 2 : 1		COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00009777		DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI	DATE 20220209
HIROSE ELECTRIC CO., LTD.		APPROVED		EJ. KUNII	20160531	DRAWING NO. EDC-023026-71-00			
		CHECKED		EJ. KUNII	20160531	PART NO. RP13A-12PH-20SC(71)			
		DESIGNED		MM. ISHII	20160531	CODE NO. CL0113-0217-7-71			
		DRAWN		MM. ISHII	20160531				