




- Notes 1 Applicable crimp contact:
Contact No. 1, 3 to 10 : RP17-PC-222/CL113-0508-0 (Applicable cable size : awg#24 to #28. Cable jacket outer diameter shall be $\phi 1.2$ mm or less.)
Contact No. 2, 11, 12 : RP17-PC-212/CL113-0507-7 (Applicable cable size : awg#18 to #22. Cable jacket outer diameter shall be $\phi 1.7$ mm or less.)
- 2 Applicable cable crimping tool : RP17-TC-01/CL150-0042-5
- 3 Extraction tool : RP6-SC-TP/CL150-0039-0
- 4 The tightening torque of Ref No. ⑧ : 0.15 to 0.2 N·m.
To prevent loosening Ref No. ⑧, use LOCTITE 243, HENKEL JAPAN or equivalent.
- 5 Shall be disassembled when delivered.
- 6 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure, please confirm before the use.

5	Brass				
4	Polycarbonate	(BLACK) UL94V-0	9	Brass	
3	Polycarbonate	(BLACK) UL94V-0	8	Brass	Black chromete treatment (Trivalent chromium) JIS B 1111 M2X0.4X4
2	Stainless steel		7	Steel	Nickel plating
1	Polycarbonate	(BLACK) UL94V-0	6	Polyvinylchloride	(BLACK)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00009784	DESIGNED TY. SUZUKI
					CHECKED HY. KOBAYASHI
					DATE 20220214
HIROSE ELECTRIC CO., LTD.		APPROVED : MO. SATOH	20060630	DRAWING NO. EDC-025906-71-71	
		CHECKED : MO. SATOH	20060630	PART NO. RP17A-13P-12PC(71)	
		DESIGNED : EM. YUMINO	20060630	CODE NO. CL0113-0551-9-71	
		DRAWN : MM. ISHII	20060614		