


Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Notes

- 1 Applicable crimp contact:  
 Contact No. 1.3 to 10  
 RP17-SC-222/CL113-0510-1 (Applicable cable size : awg#24 to #28.  
 Cable jacket outer diameter shall be  $\phi 1.2$ mm or less.)  
 Contact No. 2, 11, 12  
 RP17-PC-212/CL113-0509-2 (Applicable cable size : awg#18 to #22.  
 Cable jacket outer diameter shall be  $\phi 1.7$ mm or less.)
- 2 Applicable cable crimping tool : RP17-TC-01/CL150-0042-5
- 3 Extraction tool : RP6-SC-TP/CL150-0039-0
- ④ The tightening torque of Ref No. ④ : 0.15 to 0.2 N·m.  
 To prevent loosening Ref No. ④ , use LOCTITE 243, HENKEL JAPAN or equivalent.
- 5 Shall be disassembled when delivered.
- 6 The cable pull and twisting strength and other characteristics may differ,  
 depending on the cable structure, please confirm before the use.

3	Polycarbonate	(BLACK) UL94V-0	6	Brass	Black chromete treatment (Trivalent chromium) JIS B 1111 M2X0.4X4		
2	Polycarbonate	(BLACK) UL94V-0	5	Polyvinylchloride	(BLACK)		
1	Polycarbonate	(BLACK) UL94V-0	4	Brass			
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS		
UNITS mm		SCALE 2 : 1	COUNT ④ 2	DESCRIPTION OF REVISIONS DIS-C-00009784	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI	DATE 20220214
HIROSE ELECTRIC CO., LTD.		APPROVED : EJ. KUNII	20131118	DRAWING NO.	EDC-040741-71-71		
		CHECKED : HT. ZENBA	20131118	PART NO.	RP17-13JA-12SC(71)		
		DESIGNED : HK. NAMAI	20131118	CODE NO.	CL0113-0516-8-71	1/1	
		DRAWN : HK. NAMAI	20131118				