








Feb.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


ELV, RoHS COMPLIANT



RECOMMENDED PCB PATTERN



- NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.)
USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C
90~120s
2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
3. CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm.
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.
6. [Pattern] : Pattern prohibited area





2	BRASS	SURFACE PLATING : TIN PLATING 1μm min UNDER PLATING : NICKEL 1μm min	6	POLYESTER	
1	PA	BLACK UL94V-0	5	POLYSTYRENE	
			4	POLYIMIDE	PICK & PALCE TAPE
			3	BRASS	SURFACE PLATING : TIN PLATING 1μm min UNDER PLATING : NICKEL 1μm min
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS : mm		SCALE : 2 : 1	DESIGNED : EDC-376619-00-00		
COUNT : 1		CHECKED : OM.MIYAMOTO 20190729			DATE : 20190730
DESCRIPTION OF REVISIONS		DRAWING NO. : EDC-376619-00-00			
APPROVED : HK.UMEHARA 20190730		PART NO. : ZE05H-12DP-2V			
HIROSE ELECTRIC CO., LTD.		CODE NO. : CL752-2313-0-00			
DESIGNED : TY.ISHIGURO 20190729		1/2			
DRAWN : DS.HIROWATARI 20190712					

Feb.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


PACKING STYLE

REEL DIMENSION (FREE)

PACKING STYLE DRAWING



CARDBOARD DIMENSION (FREE)



W = (405) (mm)
 D = (405) (mm)
 H = (63) (mm)

HRS	DRAWING NO.	EDC-376619-00-00
	PART NO.	ZE05H-12DP-2V
	CODE NO.	CL752-2313-0-00
		△ 2/2