




REV. 0

DCO 143673

COIL: @ 25°C

RESISTANCE 63 OHMS $\pm$ 10%

NOMINAL VOLTAGE 5.0 VDC

MUST OPERATE 2.8 VDC

MUST RELEASE 1.7 VDC MAX., 0.23 VDC MIN

ENVIRONMENT:

VIBRATION 10 Hz TO 3000 Hz @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX.

RELEASE TIME 4.0 MS MAX.

CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 14OCT02

CK. *[Signature]* 10/19/02

CII Technologies
advanced control electronic solutions

CUST. QPL

CUST. NO. M39016/23-019L REV.

"J1MAD" RELAY

J1MAPD-5XL