




Automotive Parts > Automotive Terminals > MULTILOCK, RECEPTACLE AND TAB



Terminal Type: **Tab**

Wire Size: **22 – 20 AWG**

Mating Tab Width: **1 mm [.04 in]**

Interface Plating: **Gold (Au)**

[All MULTILOCK, RECEPTACLE AND TAB \(74\)](#)

Features

Product Type Features

Receptacle Style	180°
Primary Locking Feature	Clean Body
Sealable	No

Body Features

Terminal Seal Type	Unsealed
--------------------	----------

Contact Features

Crimp Type	F-Crimp
Contact Size	1mm
Contact Fabrication	Stamped & Formed
Terminal Type	Tab
Mating Tab Width	1 mm[.04 in]
Interface Plating	Gold (Au)
Mating Tab Thickness	.64 mm[.025 in]



Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Compatible Insulation Diameter Range	1.06 – 1.7 mm[.041 – .067 in]
Wire Size	22 – 20 AWG
Wire Size Search	.3 mm², .4 mm², .5 mm²
Tab Length	23.8 mm[.94 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Reel
Packaging Quantity	5000

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5-2836994-2
OCEAN_2.0_APPLICATOR-S-FM-067F062FA

KIT
REPRESENTATION ONLY
TE Part # 7-2836994-7
OCEAN_2.0_SPARE_PART_KIT-067F062F

KIT
REPRESENTATION ONLY
TE Part # 7-2836974-7
OC-067F062F-752-CRIMPTOOLINGKIT

TE Part # 5-2836994-1
OCEAN_2.0_APPLICATOR-S-FM-067F062F-RSM

TE Part # 2836994-2
OCEAN_2.0_APPLICATOR-S-FM-067F062FA

TE Part # 2836994-1
OCEAN_2.0_APPLICATOR-S-FM-067F062F-RSM

Also in the Series | Multilock Connector System

Automotive Connector Caps & Covers (5)

Automotive Housings(140)

Automotive Signal & Power Connector Housings(136)

Automotive Signal & Power Headers (71)




[Automotive Terminals\(76\)](#)




[Other Automotive Connector Accessories\(5\)](#)

Customers Also Bought




TE Part #170454-2
[PL 250 AM REC 18-14 0.40 X 21 PRE-TPBR](#)



TE Part #172320-2
[POSITIVE LOCK 250 \(6.3 MM\) HOUSING](#)



TE Part #CAT-M9194-T273
[MULTILOCK, RECEPTACLE AND TAB](#)



TE Part #1939605-1
[0.64/2.3 SERIES 20POS.PLUG HOUSING ASSY](#)



TE Part #2301724-6
[16POS,060 SERIES,REC HSG,UNSLD](#)




TE Part #2367826-3
[84POS,0.5 SERIES,REC HSG ASSY,SLD](#)



TE Part #2367826-4
[84POS,0.5 SERIES,REC HSG ASSY,SLD](#)



TE Part #2367834-1
[REC CONN CVR ASSY,84POS,0.5 SERIES,TYPE1](#)



TE Part #2367837-1
[REC CONN CVR ASSY,84POS,0.5 SERIES,TYPE2](#)

Documents

Product Drawings

[040III TAB NON SEALED AU](#)

[Japanese](#)

CAD Files

[3D PDF](#)

[3D](#)

Customer View Model

[ENG_CVM_CVM_1565963-2_A.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_1565963-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1565963-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[MULTILOCK Connector System](#)

English

Product Specifications

[Crimping .040III Unsealed Contact, Tab](#)

Japanese

[Application Specification](#)

Japanese

[Crimping .040III Unsealed Contact, Tab](#)

Japanese

[Application Specification](#)

Japanese