



Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **MIL Spec, TE Product Specification (114-)**
TE Certification: **Yes – Certificate Included**
Power Technology Type: **Battery, Hydraulic, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Other
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1490747-1 HYP10 HEAVY DUTY 12T HEAD	 TE Part # 324442 SPLICE,AMPOWER PARA 2	 TE Part # 325201 TERMINAL,AMPOWER 2 1/4	 TE Part # 696465-1 AMPOWER,2,3/8,Z-BEND,TIN
 TE Part # 1490745-1 HYP10 LIGHT DUTY 12T HEAD	 TE Part # 1490746-1 HYP10 LIGHT DUTY 14T HEAD	 TE Part # 325250 TERMINAL,AMPOWER 2 1/2	 TE Part # 1490749-1 HYP10 8-4/0AWG MANUAL TOOL
 TE Part # 325203 TERMINAL,AMPOWER 2 3/8	 TE Part # 326799 TERMINAL,AMPOWER 2 3/8	 TE Part # 325202 TERMINAL,AMPOWER 2 5/16	 TE Part # 696696-1 AMPOWER,2,3/8,TIN,90,30 DEG BL RIGHT



TE Part # 55817-1
TERM, AMPWR #2 3/8 BENT 90 DW

TE Part # 324457
SPLICE, AMPPOWER BUTT 2

TE Part # 696469-1
AMPPOWER, 2, 3/8, TIN, 90, 30 DEG BL

Customers Also Bought

TE Part #1490746-1
HYP10 LIGHT DUTY 14T HEAD

TE Part #4-1633713-6
CRIMPER, WIRE PREMIUM

TE Part #2151190-1
OCEAN_2.0_APPLICATOR-S-080F110OV-RSM

TE Part #7-2266116-7
OCEAN_2.0_SPARE_PART_KIT-069F110O

TE Part #2380197-1
DIE SET DIA 6MM T 16MM2

TE Part #122331-2
ANVIL, COMBINATION

TE Part #5-240641-4
SPACER, SLUG BLADE(054)

TE Part #2234158-4
ANVIL HVM F

TE Part #2-2326331-5
TONK TERMINAL

TE Part #2393553-1
INDENTER HVM 2B

Documents

Datasheets & Catalog Pages

AT-Hydraulic Crimp Tooling Solutions-1654519

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English

