

CII

TE Internal #: 1617004-9

General Purpose Power Relay, DC, Non-Polarized, Monostable, 2

Form C DPDT-CO, 10 A Contact Rating, 12 VDC Coil Voltage, 1.92

W Coil Power, Board Mount

[View on TE.com >](#)

Relays &amp; Contactors &gt; Electromechanical Relays

Relay & Contactor Type: **General Purpose Power Relay**Coil Magnetic System: **Non-Polarized, Monostable**Contact Arrangement: **2 Form C DPDT-CO**Current Type: **DC**Contact Current Rating: **10 A**

## Features

### Product Type Features

Relay &amp; Contactor Type

General Purpose Power Relay

### Configuration Features

Contact Arrangement

2 Form C DPDT-CO

### Electrical Characteristics

Coil Resistance

75 Ω

Contact Switching Voltage (Max)

28 VDC

Contact Current Rating

10 A

Coil Voltage Rating

12 VDC

Coil Power Rating DC

1.92 W

### Body Features

Enclosure Type

Hermetically Sealed

### Contact Features

Contact Material

Silver Cadmium Oxide

### Termination Features

Main Termination &amp; Connection Type

Solder Pins

Coil Termination &amp; Connection Type

Solder Pins

### Mechanical Attachment

## Product Mount Type

Board Mount

## Usage Conditions

Operating Temperature Range

-65 – 125 °C

Environmental Ambient Temperature (Max)

125 °C[257 °F]

## Operation/Application

Vibration Resistance

20G's, 10 – 2000Hz

Shock Resistance

100G's, 6ms

Coil Magnetic System

Non-Polarized, Monostable

Current Type

DC

## Other

Contact Current Class

&gt;5 – ≤10 A

Coil Power Rating Class

&gt;1.5 – ≤3 W

## Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU

Not Compliant

EU ELV Directive 2000/53/EC

Not Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025

(247)

Candidate List Declared Against: JAN 2025

(247)

SVHC &gt; Threshold:

Cd (2.75% in Component Part)

## Article Safe Usage Statements:

Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



TE Part # 1617754  
FCA-410-1517M-M83536/15-017M

## Customers Also Bought



TE Part #DT06-08SA  
PLG, 8P, GRY, N, A



TE Part #5-87589-6  
20 MODII HDR DRST SHRD .100CL



TE Part #205089-2  
PIN CONTACT,SZ 20,AMPLIMITE



TE Part #205090-2  
SKT CONT ASSY,SZ 20,AMPLIMITE




TE Part #3-641215-2  
02P MTA100 HDR ASSY FL/ST 30AU



TE Part #1617030-2  
HFW1201B00 = HFW 1/2 SIZE RELA



TE Part #1617031-1  
HFW1201K00 = HFW 1/2 SIZE RELA



TE Part #1-1617752-0  
FCA-210-CY9



TE Part #1658013-1  
MSB0.80PL5ASY040FL,-10,-TY



TE Part #6609065-2  
3EDP=F7688 SO

## Documents

**CAD Files**

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1617004-9\\_C.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1617004-9\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1617004-9\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**

[5-1773450-5\\_sec1\\_07](#)

English

[RELAY](#)

English