

404802721002 ✓ ACTIVE

Citec | Corcom M

TE Internal #: 1630949-2

470K ohm, Cermet, 10 %, 2 W, Terminates To Printed Circuit Board, Panel Mount, Single, Top Adjustment, 6.34 × 25 mm [.248 × .984 in] Shaft, Corcom M

[View on TE.com >](#)



Passive Components > Resistors > Potentiometers



Power Rating: **2 W**

Product Terminates To: **Printed Circuit Board**

Product Mount Type: **Panel Mount**

Passive Component Tolerance: **10 %**

Sealing Option: **Sealed**

Features

Product Type Features

Rotary Turn Type	Single Turn
Sealing Option	Sealed
Element Type	Cermet

Configuration Features

Number of Turns	1
Sections	Single
Adjustment Location	Top
Adjustment Method	Shaft

Electrical Characteristics

Power Rating	2 W
Passive Component Tolerance	10 %
Resistance Value	470K Ω
Resistance Class	1k Ω – 1M Ω

Body Features

Shaft Style	Plain
Product Orientation	Vertical

Termination Features

Product Terminates To	Printed Circuit Board
-----------------------	-----------------------

Mechanical Attachment

Product Mount Type

Panel Mount

Dimensions

Shaft Size

6.34 x 25 mm [.248 x .984 in]

Usage Conditions

Temperature Coefficient

0 – 60 ppm/°C

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://te.com)>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)

Candidate List Declared Against: JUNE 2023 (235)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Pin-in-Paste capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1630949-4
MCU FLUSH 470K 10% 26MM SL


Also in the Series | Corcom M




EMI & EMC Accessories(2)



Medical Power Entry Modules(10)



Potentiometers(5)



Power Entry Modules(28)

Customers Also Bought



TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts



TE Part #DT06-2S
PLG, 2P, GRY, N




TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING

Documents

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_1630949-2_K.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1630949-2_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1630949-2_K.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[Spindle Operated Potentiometers - Type M Series - Tyco Electronics Passives](#)

English