

344525-1

✓ ACTIVE


Econoseal

TE Internal #: 344525-1

Contact Insertion, Contact-to-Housing, Insertion & Extraction Tools

[View on TE.com >](#)

Application Tooling > Insertion & Extraction Tools

Insertion & Extraction Tool Type: **Contact Insertion**Insertion & Extraction Tool Application: **Contact-to-Housing**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Insertion
Insertion & Extraction Tool Application	Contact-to-Housing

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 344994-1
.250 SERIES REC. L.P.




TE Part # 344075-1
2 WAY TAB HSG.




TE Part # 344081-1
RECPT. HSG. ASSY. 2 WAY




TE Part # 344086-1
8 WAY TAB ANTI-BACKOUT




TE Part # 344992-1
ECONOSEAL III HC TAB L.P.



TE Part # 344996-1
ECONOSEAL III HC REC L.P.



TE Part # 344990-1
ECONOSEAL III HC TAB L.P.



TE Part # 344067-2
.250"SPEC.F.TAB.(PLATED)



TE Part # CAT-EC7491-T273
Econoseal Receptacles and Tabs

Customers Also Bought



TE Part #1410187-3
MULTIGIG RT T2 7RW DC DF CT



TE Part #1410968-3
MULTIGIG RT2 7RW RTM DC DF CT



TE Part #1410975-3
MULTIGIG RT2 7RW DC RTM CT



TE Part #2102771-1
DC, 7Row, Center, MULTIGIG RT 2R



TE Part #2102772-1
DC, 7Row, Half Left End, MULTIGIG
RT 2R



TE Part #2226808-1
COVER, MULTIGIG DAUGHTERCARD,
6U



TE Part #6116353-1
INV MJ,1X2,PNL GRD,LED (G/Y)



TE Part #1-6450869-0
V/R
2ACP+8S+4ACP+16S+2ACP+12S+2ACP



TE Part #144127-E
ERMBGR BS GSEFT * LP16 * ERMET-
BAUSATZ F



TE Part #1410139-2
MULTIGIG RT T2 .8 DC DF F-RGT

Documents

Datasheets & Catalog Pages

CRIMPING TERMINALS

English

CRIMPING WHERE FORM MEETS FUNCTION

English