

55PC1121-26-9/96-9

✓ ACTIVE

RAYCHEM

TE Internal #: 437277-000

600 VAC, Tin-Coated Copper, 26 AWG, -65 – 150 °C, Twisted Pair Cable

[View on TE.com >](#)

Wire & Cable > Twisted Pair Cable > 2 Core Twisted Pair Cable: Tin Coated Copper Cable, 26-28 AWG

Operating Temperature Range: **-65 – 150 °C [-85 – 302 °F]**Cable Type: **Spec 55**Operating Voltage: **600 VAC**Wire & Cable Insulation Material: **Modified Radiation Cross-linked ETFE Polymer**Conductor Material: **Tin-Coated Copper****[All 2 Core Twisted Pair Cable: Tin Coated Copper Cable, 26-28 AWG \(11\)](#)**

Features

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Wire & Cable Insulation Material	Modified Radiation Cross-linked ETFE Polymer
----------------------------------	--

Conductor Material	Tin-Coated Copper
--------------------	-------------------

Dimensions

Wire Size	26 AWG
-----------	--------

Usage Conditions

Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]
-----------------------------	----------------------------

Cable Type	Spec 55
------------	---------

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006
--

Halogen Content

Current ECHA Candidate List: JAN 2025

(247)

Candidate List Declared Against: JAN 2025

(247)

Does not contain REACH SVHC

Solder Process Capability

Out of Scope - excluded from Halogen requirements

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 650074-000
D-436-36

Customers Also Bought



TE Part #430079-000
7528A5314-0




TE Part #383059-000
44A0131-22-0/2/9



TE Part #803753-SF
FN9222B-6-06



TE Part #838503-000
55PC0111-26-9



Documents

Product Drawings

[55PC1121-26-9/96-9](#)

English

Datasheets & Catalog Pages

[Raychem Wire and Cable Quick Reference Guide](#)

English

Product Specifications

[Product Specification](#)

English