

Application Tooling &gt; Hand Crimping Tools



Tool Grade: Premium Crimp Tooling

Die Sets Type: Removable/Interchangeable

Specification Type: MIL Spec, TE Product Specification (114-)

TE Certification: Yes – Certificate Included

Power Technology Type: Battery, Hydraulic, Manual

## Features

### Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

## Product Compliance

For compliance documentation, visit the product page on TE.com >

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 324465  
SPLICE,AMPOWER BUTT 400MCM



TE Part # 326003  
TERMINAL,AMPOWER 400MCM 3/8



TE Part # 326016  
TERMINAL,AMPOWER 400MCM 0



TE Part # 326021  
TERMINAL,AMPOWER 400MCM 0



TE Part # 326005-2  
TERMINAL,AMPOWER 400MCM 1/2



TE Part # 326807-2  
400 MCM AMPOWER TERM(2)3/8 DIA



TE Part # 276963-1  
TERMINAL,AMPOWER 400MCM



TE Part # 324450  
SPLICE,AMPOWER PARA 400MCM



TE Part # 326807  
TERMINAL,AMPOWER 400MCM 3/8



TE Part # 69082  
HYP8 4/0-1000MCM 26T HEAD



TE Part # 326005  
TERMINAL,AMPOWER 400MCM 1/2

## Customers Also Bought



TE Part #F64479-000  
VERSAFIT-MINI-SPL-1/4-BK



TE Part #CAT-P592-R472A  
PIDG Ring Tongue Terminals



TE Part #33220  
TERMINAL,SOLIS R 12-10 3/8



TE Part #34123  
TERMINAL,SOLIS R 16-14 10



TE Part #35684  
TERMINAL,SOLIS R 14-12 6



TE Part #46750-2  
HYP8 AMPower 4/0AWG Die Set



TE Part #46758-2  
HYP8 AMPower 800MCM Die Set



TE Part #324445  
SPLICE,AMPower PARA 3/0



TE Part #324471  
SPLICE,AMPower BUTT 1000MCM

## Documents

### Datasheets & Catalog Pages

[AT-Hydraulic Crimp Tooling Solutions-1654519](#)

English

### Bottoming Dies

English

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English