



Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Electric, Manual
Tooling Type	Standard Die Envelope (SDE) Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC



Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 173716-5 040 HDIO REC CONT AS	 TE Part # 173681-3 040 MULTILOCK REC CONT BLANK	 TE Part # 173716-3 040 HDIO REC CONT BLANK OUT AU	 TE Part # 175061-2 040 HDIO REC CONTACT GOLD L/P
 TE Part # 173681-4 040 MULTILOCK REC CONT GOLD	 TE Part # 173716-4 040 HDIO REC CONT BLANK OUT	 TE Part # 173681-6 040 RCPT NON SEALED TIN	 TE Part # 175062-2 040 MULTILOCK REC CONT. L/P
 TE Part # CAT-M9194-T273 MULTILOCK, RECEPTACLE AND TAB			

Customers Also Bought




TE Part #11027286-00
44008RC, THERM, ROHS



TE Part #280621-2
MOD I CONT STRIP



TE Part #2-747579-7
SHLDING FERRULE, PLTD TIN, BULK



TE Part #776273-4
14POS, AMPSEAL, SOC HSG ASSY, SLD, COD 4



TE Part #1337772-4
50/OHM COAX BNC STR PLUG ELB P



TE Part #1-1676913-5
YR1 0.1% 1K54



TE Part #6-1676915-3
YR1 0.1% 11K5



TE Part #2138530-1
STRAIN RELIEF, 14 POSITION AMPSEAL



TE Part #1-2273034-1
M12 x 1.0 straight plug pigt A



TE Part #DT06-08SA-KIT
DT06-08SA AND WEG ONLY

Documents

Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English