

D-146-0207


✓ ACTIVE

RAYCHEM

TE Internal #: 624512-000

4.6 mm [.181 in] Expanded Inside, Shrinks To 1.78 mm [.07 in], Pre-Installed Lead, 22 AWG, .34 mm² Wire, SolderSleeve Shield Terminators[View on TE.com >](#)

Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



Operating Temperature (Max): 150 °C [302 °F]

Expanded Inside Diameter (Min): 4.6 mm [.181 in]

Recovered Inside Diameter (Max): 1.78 mm [.07 in]

Pre-Installed Lead: Yes

Wire Size: .34 mm²

Features

Configuration Features

Pre-Installed Lead	Yes
--------------------	-----

Dimensions

Expanded Inside Diameter (Min)	4.6 mm [.181 in]
Recovered Inside Diameter (Max)	1.78 mm [.07 in]
Wire Size	22 AWG

Usage Conditions

Operating Temperature (Max)	150 °C [302 °F]
Wire Temperature (Max)	125 °C

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (37% in Solder)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EG8162-000
HL1920E-230V-EURO


Customers Also Bought



TE Part #CAT-AS22759-34
SAE AS22759: 34/35/41/42/43 - Dual-Wall, Normal Weight Wire




TE Part #284303-000
B-020-22-N



TE Part #38943-20L
CONT SOC ASSY



TE Part #610004-000
D-300-01



TE Part #620005-000
D-104-00



TE Part #205209-2
RECP ASSY SIZE 4



TE Part #211600-2
DUST COVER,SZ 2,NIC 600



TE Part #328308
SPARE WIRE CAP,BLU, 16-14 AWG



TE Part #2-342143-1
TAPE MOUNTED 16-14 F.E. TERMIN

Documents

Product Drawings

D-146-0207

English

Product Specifications

[Product Specification](#)

English