





REVISIONS				
P	LTN	DESCRIPTION	DATE	APVD
A		INITIAL RELEASE	17APR2024	RZ HL
A1		REVISED PER ECR-26-271720	23FEB2026	MK SSM



- NOTES:
- 1. MATERIAL:
HOUSING: LCP, BLACK, UL 94V-0
SIGNAL CONTACT: COPPER ALLOY
GROUND SHIELD: COPPER ALLOY
 - 2. FINISH: CONTACT AND SHIELD
MATING AREA:
MEET PERFORMANCE REQUIREMENT OF TE CONNECTIVITY
PRODUCT SPECIFICATION 108-115174.

COMPLIANT PIN AREA:
0.5um MIN MATTE TIN OVER NICKEL UNDERPLATING.
 - 3. PLATING THROUGH HOLE SPECIFICATION:
SIGNAL VIA
DRILL HOLE : 0.40±0.020,
COPPER PLATING: 0.0375±0.0125,
FINISH HOLE: 0.31 REF
GROUND VIA
DRILL HOLE: 0.45±0.020,
COPPER PLATING 0.0375±0.0125,
FINISH HOLE: 0.36 REF

MORE INFORMATION ABOUT PLATING THROUGH HOLE PLEASE
REFER TO APPLICATION SPECIFICATION.
 - 4. DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
 - 5. PART NUMBER, DATE CODE MARKING IN APPROXIMATE AREA AS SHOWN.



RECOMMENDED PCB LAYOUT
VIEW FROM COMPONENT SIDE

2472335-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: RICHARD ZHOU 10AUG2023	TE Connectivity	
DIMENSIONS: mm		CHK: MIKE CHEN 10AUG2023	NAME: ASSEMBLY DRAWING	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: HOPE LU 10AUG2023	eZd PLUS PLUS, VERTICAL, HEADER	
0 PLC ±0.2	1 PLC ±0.2	PRODUCT SPEC	108-115174	
2 PLC ±0.2	3 PLC ±0.2	APPLICATION SPEC	114-160011	
4 PLC ±0.2	ANGLES ±0.2	FINISH	SIZE: 114-160011	CAGE CODE: 100779
MATERIAL: TBD	FINISH: 1	WEIGHT: -	DRAWING NO: 2472335	RESTRICTED TO: -
CUSTOMER DRAWING		SCALE: 8:1	SHEET: 1 OF 1	REV: A1