

4

3





2

1


THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
20
© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
ES	00	P	LTR	DESCRIPTION	DATE	DWN APVD
			A	INITIAL RELEASE	04MAY2011	S.W S.Y
			B	REVISED	19JAN2012	S.W S.Y
			BI	REVICED	12DEC2022	M.T H.T

1932768-1: AS SHOWN



1. CONTACT: COPPER ALLOY
ALL OVER Ni: 1.27um MIN.
CONTACT AREA PdNi: 1.0um MIN. Au: 0.2um MIN.
SOLDERING AREA Au: 0.05um MIN.
- CLIP: SUS
ALL OVER Ni: 1.3um MIN.
Tin: 1um MIN(ZONE I).
- HOUSING: THERMOPLASTIC
2. RECOMMENDED SOLDERING THICKNESS: 100um MIN.
RECOMMENDED SOLDERING AREA:
100% OF REFERENCE LAYOUT PATTERN
3. COPLANARITY: 0.1MAX. (SEE FIG.1)
REFERENCE PICK & PLACE AREA.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	3DEC2010	 TE Connectivity		
		CHK	3DEC2010			
		APVD	3DEC2010			
		PRODUCT SPEC	3DEC2010			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.15		NAME SUPER LOW PROFILE SIM H=1.95 WITH FLANGE		
		0 PLC ±		SIZE		
		1 PLC ±		CAGE CODE		
		2 PLC ±		DRAWING NO		
		3 PLC ±		RESTRICTED TO		
MATERIAL		FINISH		A300779C-1932768		
		ANGLES ±5°		RIM		
		WEIGHT 0.46g		SCALE 4:1 SHEET 1 OF 2 REV BI		
		CUSTOMER DRAWING				


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



20


© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.



LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.15
	0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm 5^\circ$
MATERIAL	FINISH

DWN	 TE Connectivity					
CHK						
APVD	NAME SUPER LOW PROFILE SIM H=1.95 WITH FLANGE					
PRODUCT SPEC						
APPLICATION SPEC						
WEIGHT						
SIZE		CAGE CODE	DRAWING NO		RESTRICTED TO	
A3		00779	C-1932768		RIM	
CUSTOMER DRAWING			SCALE	4:1	SHEET 2 OF 2	REV B1