

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT 2020

TE Connectivity Ltd.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	INITIAL CUSTOMER DRAWING	12FEB2020	AFK	LS

FLATTENED WIDTH

D

d

w

EXPANDED TUBING PRODUCT

SPOOL

SPOOL I.D. 101 (4.0)

Product Size	3/32	1/8	3/16	1/4	3/8	1/2	3/4	1	1-1/2	2
"D" Minimum Supplied I.D.	2.36 (.093)	3.18 (.125)	4.75 (.187)	6.35 (.250)	9.53 (.375)	12.7 (.500)	19.05 (.750)	25.4 (1.00)	38.1 (1.50)	50.8 (2.00)
"d" Maximum Recovered I.D.	0.79 (.031)	1.07 (.042)	1.57 (.062)	2.11 (.083)	3.18 (.125)	4.22 (.166)	6.35 (.250)	8.46 (.333)	19.05 (.750)	25.4 (1.00)
"w" Recovered Wall Thickness ±0.08 (.003)	0.58 (.023)	0.58 (.023)	0.58 (.023)	0.58 (.023)	0.61 (.024)	0.61 (.024)	0.61 (.024)	0.64 (.025)	0.51 (.020)	0.64 (.025)
Minimum Sleeve Flattened Width	4.45 (.175)	5.84 (.230)	8.00 (.315)	10.7 (.420)	15.5 (.610)	20.4 (.803)	30.5 (1.20)	40.4 (1.59)	60.3 (2.37)	80.0 (3.15)

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS (inches).

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL

CROSSLINKED POLYOLEFIN

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN AFK 12FEB2020

CHK -

APVD LS 12FEB2020

PRODUCT SPEC RW-2511

APPLICATION SPEC -

WEIGHT VARIOUS

CUSTOMER DRAWING

TE Connectivity

NAME

TMS-CT
OUTSIDE PRINTER SPOOL

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A30198G

C-MCD170011

-

SCALE -

SHEET 1 OF 1

REV 2

1470-19 (1/15)