

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	Y1	ECR-25-239014	17NOV2025	SA	PS

D

D

C





C

B

B

A

A



OBSOLETE 9	8	7	64.01 [2.520]	65.91 [2.595]	24	25	7-103634-4
	8	7	61.47 [2.420]	63.37 [2.495]	23	24	7-103634-3
	8	7	58.93 [2.320]	60.83 [2.395]	22	23	7-103634-2
	8	7	56.39 [2.220]	58.29 [2.295]	21	22	7-103634-1
	8	7	53.85 [2.120]	55.75 [2.195]	20	21	7-103634-0
	8	7	51.31 [2.020]	53.21 [2.095]	19	20	6-103634-9
	8	7	48.77 [1.920]	50.67 [1.995]	18	19	6-103634-8
OBSOLETE	8	7	46.23 [1.820]	48.13 [1.895]	17	18	6-103634-7
OBSOLETE	8	7	43.69 [1.720]	45.59 [1.795]	16	17	6-103634-6
OBSOLETE	8	7	41.15 [1.620]	43.05 [1.695]	15	16	6-103634-5
	8	7	38.61 [1.520]	40.51 [1.595]	14	15	6-103634-4
	8	7	36.07 [1.420]	37.97 [1.495]	13	14	6-103634-3
	8	7	33.53 [1.320]	35.43 [1.395]	12	13	6-103634-2
	8	7	30.99 [1.220]	32.89 [1.295]	11	12	6-103634-1
	8	7	28.45 [1.120]	30.35 [1.195]	10	11	6-103634-0
	8	7	25.91 [1.020]	27.81 [1.095]	9	10	5-103634-9
OBSOLETE	8	7	23.37 [.920]	25.27 [.995]	8	9	5-103634-8
	8	7	20.83 [.820]	22.73 [.895]	7	8	5-103634-7
	8	7	18.29 [.720]	20.19 [.795]	6	7	5-103634-6
	8	7	15.75 [.620]	17.65 [.695]	5	6	5-103634-5
	8	7	13.21 [.520]	15.11 [.595]	4	5	5-103634-4
	8	7	10.67 [.420]	12.57 [.495]	3	4	5-103634-3
	8	7	8.13 [.320]	10.03 [.395]	2	3	5-103634-2
OBSOLETE	8	7	5.59 [.220]	7.49 [.295]	1	2	5-103634-1
	8	7					
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.	

- 1 .000100 BRIGHT TIN-LEAD OVER .000050 NICKEL.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- 4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS. ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- 5 .000100 BRIGHT TIN OVER .000050 NICKEL.
- 6 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 7 .000100 MATTE TIN OVER .000050 NICKEL.
- 8 HIGH TEMPERATURE CONFIGURATION
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 10 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

OBSOLETE	8	5	30.99 [1.220]	32.89 [1.295]	11	12	3-103634-4
OBSOLETE	8	5	25.91 [1.020]	27.81 [1.095]	9	10	3-103634-3
OBSOLETE	8	5	23.37 [.920]	25.27 [.995]	8	9	3-103634-2
OBSOLETE	8	5	18.29 [.720]	20.19 [.795]	6	7	3-103634-1
OBSOLETE	8	5	15.75 [.620]	17.65 [.695]	5	6	3-103634-0
OBSOLETE	8	5	5.59 [.220]	7.49 [.295]	1	2	2-103634-9
OBSOLETE	8	5	41.15 [1.620]	43.05 [1.695]	15	16	2-103634-8
OBSOLETE	8	5	13.21 [.520]	15.11 [.595]	4	5	2-103634-7
OBSOLETE	8	5	10.67 [.420]	12.57 [.495]	3	4	2-103634-6
OBSOLETE	8	5	8.13 [.320]	10.03 [.395]	2	3	2-103634-5
OBSOLETE	8	1	64.01 [2.520]	65.91 [2.595]	24	25	2-103634-4
OBSOLETE	8	1	61.47 [2.420]	63.37 [2.495]	23	24	2-103634-3
OBSOLETE	8	1	58.93 [2.320]	60.83 [2.395]	22	23	2-103634-2
OBSOLETE	8	1	56.39 [2.220]	58.29 [2.295]	21	22	2-103634-1
OBSOLETE	8	1	53.85 [2.120]	55.75 [2.195]	20	21	2-103634-0
OBSOLETE	8	1	51.31 [2.020]	53.21 [2.095]	19	20	1-103634-9
OBSOLETE	8	1	48.77 [1.920]	50.67 [1.995]	18	19	1-103634-8
OBSOLETE	8	1	46.23 [1.820]	48.13 [1.895]	17	18	1-103634-7
OBSOLETE	8	1	43.69 [1.720]	45.59 [1.795]	16	17	1-103634-6
OBSOLETE	8	1	41.15 [1.620]	43.05 [1.695]	15	16	1-103634-5
OBSOLETE	8	1	38.61 [1.520]	40.51 [1.595]	14	15	1-103634-4
OBSOLETE	8	1	36.07 [1.420]	37.97 [1.495]	13	14	1-103634-3
OBSOLETE	8	1	33.53 [1.320]	35.43 [1.395]	12	13	1-103634-2
OBSOLETE	8	1	30.99 [1.220]	32.89 [1.295]	11	12	1-103634-1
OBSOLETE	8	1	28.45 [1.120]	30.35 [1.195]	10	11	1-103634-0
OBSOLETE	8	1	25.91 [1.020]	27.81 [1.095]	9	10	103634-9
OBSOLETE	8	1	23.37 [.920]	25.27 [.995]	8	9	103634-8
OBSOLETE	8	1	20.83 [.820]	22.73 [.895]	7	8	103634-7
OBSOLETE	8	1	18.29 [.720]	20.19 [.795]	6	7	103634-6
OBSOLETE	8	1	15.75 [.620]	17.65 [.695]	5	6	103634-5
OBSOLETE	8	1	13.21 [.520]	15.11 [.595]	4	5	103634-4
OBSOLETE	8	1	10.67 [.420]	12.57 [.495]	3	4	103634-3
OBSOLETE	8	1	8.13 [.320]	10.03 [.395]	2	3	103634-2
OBSOLETE	8	1	5.59 [.220]	7.49 [.295]	1	2	103634-1
REMARK	PLATING	C	B	A	NO. OF POSN	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES

± -
± -
± -
± -
± -
± -

MATERIAL
HOUSING: FLAME RETARDANT
LOF,COLOR: BLACK
CONTACTS: BRASS

FINISH
SEE TABLE

DWN
S. SHUEY
3-5-91

CHK
L. CASTAGNA
3-27-91

APVD
L. CASTAGNA
3-27-91

NAME

PRODUCT SPEC
108-25034

APPLICATION SPEC
114-25026

WEIGHT

CUSTOMER DRAWING

TE Connectivity

HDRASSY,RTANGLE,SINGLEROW,
2.54[.100]C/L0.64[.025]SQPST,
WITHPLZN&LATCHING,AMPMODULE

SIZE
A1

CAGE CODE
00779

DRAWING NO
103634

RESTRICTED TO
-

SCALE
4:1

SHEET
1

OF
1

REV
Y1