




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K3	ECR-25-239014	26APR2025	ABS	PS



CONTACT IDENTIFICATION LETTER "B" (LOCATED IN THIS AREA)

11	OBSOLETE	10	2	2.40	1.198	1-103688-1	12	6-103976-1
	OBSOLETE	10	2	2.20	1.098	1-103688-0	11	6-103976-0
	OBSOLETE	10	2	2.00	.998	103688-9	10	5-103976-9
	OBSOLETE	10	2	1.80	.898	103688-8	9	5-103976-8
	OBSOLETE	10	2	1.60	.798	103688-7	8	5-103976-7
	OBSOLETE	10	2	1.40	.698	103688-6	7	5-103976-6
		10	4	2.39	.598	103688-5	6	5-103976-5
		10	4	1.99	.498	103688-4	5	5-103976-4
		10	5	1.99	.398	103688-3	4	5-103976-3
	OBSOLETE	10	8	2.40	.298	103688-2	3	5-103976-2
		10	10	2.00	.198	103688-1	2	5-103976-1
11	OBSOLETE	9	2	2.40	1.198	1-103688-1	12	1-103976-1
	OBSOLETE	9	2	2.20	1.098	1-103688-0	11	1-103976-0
	OBSOLETE	9	2	2.00	.998	103688-9	10	103976-9
	OBSOLETE	9	2	1.80	.898	103688-8	9	103976-8
	OBSOLETE	9	2	1.60	.798	103688-7	8	103976-7
11	OBSOLETE	9	2	1.40	.698	103688-6	7	103976-6
	SUPERSEDED BY 5-103976-5	9	4	2.39	.598	103688-5	6	103976-5
		9	4	1.99	.498	103688-4	5	103976-4
	SUPERSEDED BY 5-103976-3	9	5	1.99	.398	103688-3	4	103976-3
	OBSOLETE	9	8	2.40	.298	103688-2	3	103976-2
	SUPERSEDED BY 5-103976-1	9	10	2.00	.198	103688-1	2	103976-1
	PLATING	6	B	A	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER ON STRIP	



EXAMPLE: STRIP ASSEMBLY SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: L.MAYER 05 NOV 86
CHK: P.C.DEJONG 12-11-86
APVD: P.C.DEJONG 12-11-86

DIMENSIONS: INCHES
TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± .02
3 PLC ± .005
4 PLC ± -
ANGLES ± -

PRODUCT SPEC: 108-25034
APPLICATION SPEC: 114-25026

MATERIAL: HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR: BLACK, CONTACTS: PHOS BRONZE
FINISH: SEE TABLE

WEIGHT: -
CUSTOMER DRAWING

TE Connectivity
RCPT ASSY, AMPMODU MTE, SINGLE ROW, .100 C/L, FOR NOS22-NOS26 AWG WIRE SIZE, STRIP FORM

SIZE: A2
CAGE CODE: 00779
DRAWING NO: C=103976
RESTRICTED TO: -

SCALE: 4:1
SHEET: 1 OF 1
REV: K3