


[Click here for the 3D model.](#)

#### General Information

Series	PHE844/F844
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Safety Class	X1
Qualifications	ENECL, UL, cUL
AEC-Q200	No
THB Performance	Yes
Typical Component Weight	4.611 g
Miscellaneous	ClimCat: 40/105/56/B.

#### Dimensions

L	26mm MAX	Capacitance	0.1 uF
H	16mm MAX	Tolerance	10%
T	8mm MAX	Voltage DC	1000 VDC
S	22.5mm +/-0.4mm	Voltage AC	440 VAC (X1) (ENECL), 480 VAC (UL, cUL)
LL	6mm -1mm	Temperature Range	-40/+105°C
F	0.8mm +/-0.05mm	Rated Temperature	105°C

#### Packaging Specifications

Packaging	Tray	Dissipation Factor	0.1% 1kHz, 0.2% 10kHz, 0.6% 100kHz
Packaging Quantity	186	Insulation Resistance	30 GOhms

Insulation Resistance: 30 GOhms

Max dV/dt: 100 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.