




- 1

STAMP AMP 16-14* APPROX AS SHOWN
- 2

MAXIMUM LENGTH DOES NOT INCLUDE MANUFACTURING TABS
- 3

MATERIAL: COPPER PER ASTM B-152 ANNEALED
- 4

FINISH: TIN PLATE 0.00254 [.000100] MIN EXT THK PER ASTM B-545
- 5

FINISH: TIN/LEAD (60/40) PLATE, 0.00254 [.000100] MIN EXT THK PER SAE-AMS-P-81728
- 6

NOTE DELETED
- 7

UL LISTED E13288, 16-14 AWG SOLID OR STRANDED
- 8

CSA CERTIFIED LR7189, 16-14 AWG SOLID OR STRANDED
- 9

NOTE DELETED
- 10

GOLD PLATE 0.00127[.000050] MIN EXT THK PER ASTM B488, TYPE1, CODE C OVER NICKEL PLATE 0.00127[.000050] MIN EXT THK PER SAE AMS QQ-N-290 OVER Cu FLASH PER SAE AMS 2418

170°C[338°F]	7 8	4	100	LOOSE PIECE, BOX	8-34137-1
260°C[500°F]	----	10	1000	LOOSE PIECE	34137-4
170°C[338°F]	----	5	1000	LOOSE PIECE	34137-3
170°C[338°F]	7 8	4	1000	LOOSE PIECE	34137
MAX TEMP	APPROVALS	FINISH	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 1.04-2.62mm²[2,050-5,180] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-13-93	STE TE Connectivity Ltd.		
DIMENSIONS: mm [INCHES]		CHK DA PATTERSON 4-13-93			
		APVD DA PATTERSON 4-13-93	NAME		
		PRODUCT SPEC UL 486 C	SPLICE, PARALLEL, SOLISTRAND 16-14 AWG		
MATERIAL - 3		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± - FINISH SEE TABLE	APPLICATION SPEC -	SIZE A2	CAGE CODE 00779
			WEIGHT	DRAWING NO C=34137	RESTRICTED TO -
			CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1
				REV N2	