


PHE850EB5330MB12R17

Aliases (F850BM333M300A)

Not for New Design

PHE850/F850, Film, Metallized Polypropylene, Safety, 0.033 uF, 20%, 1,250 VDC, 300 VAC (Y2), 110°C, 15 mm



Click [here](#) for the 3D model.

General Information

Series	PHE850/F850
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Safety Class	Y2
Qualifications	ENEC, UL, cUL
AEC-Q200	No
Typical Component Weight	3.044 g
Notes	Not For New Design, Please Check Possible Alternative Parts in R41.

Dimensions

L	18mm MAX
H	15mm MAX
T	8mm MAX
S	15mm +/-0.4mm
LL	17mm NOM
F	0.8mm NOM

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	400

Specifications

Capacitance	0.033 uF
Tolerance	20%
Voltage DC	1250 VDC
Voltage AC	300 VAC (Y2)
Temperature Range	-55/+110°C
Rated Temperature	110°C
Dissipation Factor	0.15% 1kHz, 0.2% 10kHz, 0.6% 100kHz
Insulation Resistance	30 GOhms
Max dV/dt	100 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.