





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AF	50					
		C2		ECR-15-005665	10AUG2015	BDA
						PKS

- 1
- CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59±0.08 [.220±.003] CENTERS.
- 2
- SLOT ACCEPTS A SINGLE WIRE MAX OF 0.64–0.81mm [#22–#20] AWG COPPER MAGNET WIRE.
SLOT ACCEPTS A SINGLE WIRE MAX OF 0.72–0.91mm [#21–#19] AWG ALUMINUM MAGNET WIRE.
ALUMINUM WIRE RANGE APPLIES FOR POST-TIN PLATED VERSIONS ONLY.
- 3
- AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER 23NOV1998	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK PHILLIP M. FORTNEY 23NOV1998				
		APVD PETE DESANTIS 23NOV1998	NAME TAB, 4.75[.187] FASTON™ 300 SERIES MAG-MATE™			
		PRODUCT SPEC 108-2012				
		APPLICATION SPEC 114-2046	SIZE A2	CAGE CODE 00779	DRAWING NO C=1217128	RESTRICTED TO -
MATERIAL BRASS		FINISH TIN PLATE	WEIGHT -	SCALE 10:1	SHEET 1 OF 1	REV C2
CUSTOMER DRAWING						