

MINIATURE HERMAPHRODITIC CONNECTOR SYSTEM

LOW PROFILE BOARD TO BOARD AND WIRE TO BOARD CONNECTORS

The low profile SMT miniature hermaphroditic board-to-board connectors are designed to provide power between adjacent linear printed circuit boards. Ideal for use in compact spaces with features designed for vacuum pick and place that make it suitable for high volume automated manufacturing.

ELECTRICAL

- Current Rating: 3 A max.
- Voltage Rating: 300 VAC / DC (UL)
50 VAC / DC (TUV)
- Dielectric Withstanding Voltage: 1600 VAC

MECHANICAL

- Operating Temperature: -40°C to +105°C (UL)
-35°C to 65°C (TUV)

MATERIALS

- Housing: High temperature thermoplastic UL 94V-0
- Contacts: Copper alloy, tin over nickel plated

STANDARDS AND SPECIFICATIONS

- Product Specification: 108-106050
- Application Specification: [114-106050](#)
- UL and cUL Recognized: File No. E321453
- EN 60838-1 & EN 60838-2-2: Certificate No. 50280860

KEY BENEFITS

- Reduce assembly time, minimize inventory and lower production costs with connectors that mate and un-mate to themselves horizontally and vertically
- Connect data and control signals with 2, 4 and 6 position hermaphroditic versions
- Automate production with flat top surface for vacuum pick and place assembly
- Support re-flow processing with high temperature material

APPLICATIONS

- Architectural and sign lighting
- Retail and display lighting
- Fluorescent LED retrofit lighting
- Cabinet or furniture lighting
- Commercial / residential cove lighting
- Access control equipment
- Thermostats
- Vending machines



MINIATURE HERMAPHRODITIC CONNECTOR SYSTEM

PRODUCT OFFERING

Part Number	Description
1971567-1	2 position hermaphroditic board to board connector
1971567-2	4 position hermaphroditic board to board connector
1971567-3	6 position hermaphroditic board to board connector
2213203-1	2 position mini hermaphroditic insert molded wire to board lead assembly (mates with 1971567-1)
1971742-1	1 position blade board to board connector
1971743-1	1 position receptacle board to board connector
2213610-1	2 position mini hermaphroditic assy with posts
2213610-2	4 position mini hermaphroditic assy with posts
2213610-3	6 position mini hermaphroditic assy with posts

MINIATURE HERMAPHRODITIC CONNECTOR SYSTEM

DIMENSIONS




2, 4 and 6 position showing 2 mated parts



¹ All features and dimensions of 2, 4 and 6 position versions are the same except as shown

PCB Layout and Packaging Details


Horizontal mating and unmating only
with 0.2 mm gap between PCBs



Horizontal and vertical mating and unmating
with 2.4 mm gap between PCBs







6P	19.30	32.00	1971567-3
4P	13.30	24.00	1971567-2
2P	7.30	16.00	1971567-1
POSITION	DIM.C	DIM.B	FOR P/N



1 position receptacle

1 position blade

2 position mini hermaphroditic wire to board lead assembly





2 position wire to board lead assembly is secured to heat sink with thermally conductive double sided tape

MINIATURE HERMAPHRODITIC CONNECTOR SYSTEM

DIMENSIONS

2, 4 and 6 position Mini Hermaphroditic Connectors¹




2, 4 and 6 position showing 2 mated parts



¹ All features and dimensions of 2, 4 and 6 position versions are the same except as shown

PCB Layout and Packaging Details


Horizontal mating and unmating only
with 0.2 mm gap between PCBs




Horizontal and vertical mating and unmating
with 2.4 mm gap between PCBs




6P	19.30	32.00	2213610-3
4P	13.30	24.00	2213610-2
2P	7.30	16.00	2213610-1
POSITION	DIM.C	DIM.B	FOR P/N





1 position receptacle



1 position blade



2 position mini hermaphroditic wire to board lead assembly



2 position wire to board lead assembly is secured to heat sink with thermally conductive double sided tape

Dimensions are shown in millimeters for reference purposes only. Specifications subject to change. Customer drawing should be used for all design activity.

MINIATURE HERMAPHRODITIC CONNECTOR SYSTEM

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
The Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

Connect With Us

We make it easy to connect with our experts and are ready to provide all the support you need.

Visit te.com/support to chat with a Product Information Specialist.

te.com/hermaphroditic-connectors

TE Connectivity, TE, TE connectivity (logo) and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

©2026 TE Connectivity. All Rights Reserved.

01-26