





NOTES:
1. PEELING RESISTANCE: 0.196N(20gf)–0.686N(70gf)
SPEED: 300mm/min

TOLERANCE UNLESS OTHERWISE SPECIFIED

10>* 30>*>10 100>*>30 ANGLE	:±0.2 :±0.25 :±0.3 :±3°
--------------------------------------	----------------------------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	DWN JACH HOU 19SEP10 CHK MARTIN LI 19SEP10 APVD STEVEN YAO 19SEP10 PRODUCT SPEC 108-60016 APPLICATION SPEC WEIGHT CUSTOMER DRAWING
MATERIAL	FINISH	

TE Connectivity Ltd.

EMBOSS
CT HEADER ASSY
BOX V SMT

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-292175	—
SCALE	N/A	SHEET 1 OF 3	REV B4

4



3

2

1


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




SECT "B"- "B"

- NOTES;
- 2. MATERIAL:HSG-NYLON (UL94V-0)
COLOR:NATURAL, BLACK
POST:TIN BRASS
TAIL: TIN BRASS
 - 3. OCCUPANT AREA ON PC BOARD
 - 4. TO BE MEASURED WITH CONNECTOR PLACED ON HORIZONTAL DATUM SURFACE,FLOAT OF SOLDER TINE AND TAIL FROM DATUM SURFACE IS 0.1mm MAX




SECT "A"-"A"




RECOMENOED P.C.BOARD LAYOUT
(P.C.B THK:0.8mm MIN)

16.0	19.8	9	2-292175-9	292175-9
14.0	17.8	8	2- -8	-8
12.0	15.8	7	2- -7	-7
10.0	13.8	6	2- -6	-6
8.0	11.8	5	2- -5	-5
6.0	9.8	4	2- -4	-4
4.0	7.8	3	2- -3	-3
2.0	5.8	2	2-292175-2	292175-2
F	E	POS.	BLACK	NATURAL
P/N				



3 P




2 P

TOLERANCES UNLESS OTHERWISE SPECIFIED:
10>* : ±0.2
30>* >10 : ±0.25
100>* >30 : ±0.3
ANGEL : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

FINISH
SEE NOTE

DWN -

CHK -

APVD -

PRODUCT SPEC

108-60016

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING




TE Connectivity Ltd.

ON TAPING (EMBOSS)
SMT TYPE POST HDR ASS'Y(V)
W/O BOSS &WITH TAIL TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-292175	-


SCALE N/A SHEET 2 of 3 REV B4




2. MATERIAL:HSG-NYLON (UL94V-0)
COLOR:NATURAL,BLACK
POST:TIN BRASS
TAIL: TIN BRASS

-
- NO ACCUMULATED TOLERANCE
- CIRCUIT No.1
(BASIS PIN)
- ±0.15
2.45
±0.1
F
3.05
±0.15
1.2
- TYP 1.8 MIN
PITCH
2
- ±0.1
1.2
±0.1
2.4
- TYP 3.3 MIN
- 3

RECOMENOE P.C.BOARD LAYOUT
(P.C.B THK:0.8mm MIN)



THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± —
	1 PLC ± —
	2 PLC ± —
	3 PLC ± —
	4 PLC ± —
	ANGLES ± —
MATERIAL	FINISH
SEE NOTE	SEE NOTE

DWN	—
CHK	—
APVD	—
PRODUCT SPEC	
108-60016	
APPLICATION SPEC	
WEIGHT	
CUSTOMER DRAWING	

ON TAPING (EMBOSS)
SMT TYPE POST HDR ASS'Y(V)
W/O BOSS & WITH TAIL TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
A3	00779	C-292175	—		
		SCALE	N/A	SHEET	3 OF 3
				REV	B4

16.0	19.8	9	2-292175-9	292175-9
14.0	17.8	8	2-  -8	 -8
12.0	15.8	7	2-  -7	 -7
10.0	13.8	6	2-  -6	 -6
8.0	11.8	5	2-  -5	 -5
6.0	9.8	4	2-  -4	 -4
4.0	7.8	3	2-  -3	 -3
2.0	5.8	2	2-292175-2	292175-2
F	E	POS.	BLACK	NATURAL
			P/N	