





REV. 0
DCD 143750

COIL: @ 25°C
 RESISTANCE $1560 \text{ OHMS} \pm 10\%$
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 14.2 VDC
 MUST RELEASE $8.0 \text{ VDC MAX, } 1.37 \text{ VDC MIN.}$

ENVIRONMENT:
 VIBRATION $10 \text{ Hz TO } 3000 \text{ Hz @ } 30 \text{ g's}$
 SHOCK $75 \text{ g's } 6 \text{ MS. DURATION}$
 TEMPERATURE $-65^{\circ}\text{C TO } +125^{\circ}\text{C}$
 NOTES: OPERATE TIME 2.0 MS MAX
 RELEASE TIME 4.0 MS MAX
 CONTACT STABILIZATION 2.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: $\text{LOW LEVEL TO } 1 \text{ AMP}$
 $28 \text{ VDC RESISTIVE } 100,000 \text{ OPERATIONS}$

DR. B.D. 06MAY03

CK. *[Signature]* 5/6/03

CII Technologies
 advanced control electronic solutions

CUST. QPL
 CUST. NO. M39016/18-030M REV. REV.

"JMGAD" RELAY

JMGAPD-26M