

4

3

2

1

THIS DRAWING IS UNPUBLISHED.






RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
DWDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
G		REVISED AS PER ECN-22-176158	28APR2022	I.T	S.Z

RECOMMENDED PCB LAYOUT (MOUNTING SIDE)
THICKNESS 1.57mm (TOLERANCE: ±0.05)

NOTE:

- MATERIAL:
HOUSING: PA9T WITH 33% GF, UL 94V-0, COLOR: SEE TABLE.
CONTACTS: PHOSPHOR BRONZE.
SHELL: SUS304, THICKNESS=0.40MM.
MYLAR: POLYAMIDE FILM.
- FINISH:
CONTACTS: GOLD FLASH OVER 0.762μm [30μ"] MIN. PALLADIUM-NICKEL OR ALTERNATIVE 0.762μm[30u"] MIN. GOLD PLATED ON CONTACT AREA,
2.54μm [100μ"] MIN. MATTE-TIN ON SOLDER TAIL,
2.54μm [100μ"] MIN. MATTE-TIN ON SOLDER TAIL,
3.05μm [120μ"] MIN. MATTE-TIN ON SOLDER TAIL,
WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.
SHELL: 0.76μm [30μ"] MIN. NICKEL PLATED OVERALL.
0.76μm [30μ"] MIN. MATTE-TIN OVER 1.27μm [50μ"] MIN. NICKEL.
- NO DATECODE ON PRODUCT SURFACE.
- REFLOW SOLDER CAPABLE TO 260°C PER TE TEST SPEC.
109-201, CONDITION B.

△	BLACK	W/O	W/O	TAPE REEL	W/	3-1734035-2
△	BLACK	W/	W/O	TAPE REEL	W/	2-1734035-4
△	BLACK	W/O	W/O	TAPE REEL	W/	2-1734035-3
△	BLACK	W/O	N/A	TRAY	W/	2-1734035-2
△	NATURAL	W/	W/O	TAPE REEL	W/	1734035-5
△	BLACK	W/	W/O	TAPE REEL	W/	1734035-4
△	BLACK	W/O	W/	TAPE REEL	W/	1734035-3
△	BLACK	W/O	W/O	TAPE REEL	W/	1734035-2
△	BLACK	W/O	N/A	TRAY	W/	1734035-1
PLATED	HOUSING COLOR	MYLAR	LONG CARRIER & COVER TAPE	PACKAGE	POST	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN O. HU 21DEC2007

CHK S. HOU 21DEC2007

APVD W. KODAMA 21DEC2007

PRODUCT SPEC

108-57062

QUALIFICATION TEST REPORT

501-57070

WEIGHT --

CUSTOMER DRAWING

DIMENSIONS:

MM

MATERIAL
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± 0.38
1 PLC	± 0.25
2 PLC	± 0.13
3 PLC	± 0.05
4 PLC	± 0.05
ANGLES	± 3°

FINISH
SEE NOTE

TE Connectivity

NAME

MINI USB, R/A, SMT, B TYPE

SIZE

A300779

CAGE CODE

DRAWING NO

C=1734035

RESTRICTED TO

—

SCALE

—

SHEET

1 OF 4

REV

G

4

3

2

1

THIS DRAWING IS UNPUBLISHED.







RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
DWDIST
—

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			

RECOMMENDED PCB LAYOUT (MOUNTING SIDE)
THICKNESS 1.57mm (TOLERANCE:±0.05)

NOTE:

- MATERIAL:
HOUSING: PA9T WITH 33% GF, UL 94V-0, BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
SHELL: SUS304, THICKNESS=0.40MM.
MYLAR: POLYAMIDE FILM.
- FINISH:
CONTACTS: GOLD FLASH OVER $0.762\mu\text{m}$ [$30\mu^*$] MIN. PALLADIUM-NICKEL OR ALTERNATIVE $0.762\mu\text{m}$ [$30\mu^*$] MIN. GOLD PLATED ON CONTACT AREA, $2.54\mu\text{m}$ [$100\mu^*$] MIN. MATTE-TIN ON SOLDER TAIL, WITH ENTIRE CONTACT UNDERPLATED $1.27\mu\text{m}$ [$50\mu^*$] MIN. NICKEL.
SHELL: $1.27\mu\text{m}$ [$50\mu^*$] MIN. NICKEL PLATED OVERALL.
- NO DATECODE ON PRODUCT SURFACE.
- REFLOW SOLDER CAPABLE TO 260°C PER TE TEST SPEC. 109-201, CONDITION B.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± 0.38
1 PLC	± 0.25
2 PLC	± 0.13
3 PLC	± 0.05
4 PLC	± 0.05
ANGLES	± 3°

FINISH

SEE NOTE

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

W/	W/O	TAPE REEL	W/O	4-1734035-2
W/O	W/	TAPE REEL	W/O	1-1734035-3
W/O	W/O	TAPE REEL	W/O	1-1734035-2
W/O	N/A	TRAY	W/O	1-1734035-1
MYLAR	LONG CARRIER & COVER TAPE	PACKAGE	POST	PART NUMBER



TE Connectivity

NAME

MINI USB, R/A, SMT, B TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=1734035

SCALE

SHEET

2 OF 4

REV G

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT

-

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR


DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.




PVC

PAPER BOARD

PVC

28 LAYERS

OUTER CARTON



8.25 Kg	5.55 Kg	150	56	8400 PCS	2-1734035-1
					1-1734035-1
					1734035-1
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAYS /CARTON	QUANTITY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC


APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

MM



MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

FINISH



TE Connectivity

NAME

MINI USB, R/A, SMT, B TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=1734035

SCALE






SHEET

3 OF 4

REV G


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
DW	—	P	LTR	DESCRIPTION	DATE	DWN APVD
				SEE SHEET 1.		




OUT BOX PACKAGE DIAGRAM DRAWING

FOR 1734035-3, 1-1734035-3 AND 2-1734035-3 (LONG CARRIER & COVER TAPE)



FOR 1734035-2, 1734035-4, 1734035-5, 1-1734035-2, 3-1734035-2, 2-1734035-2, 2-1734035-4, 4-1734035-2



4.95 Kg	2.31 Kg	700	5	3500	W/	W/O	4-1734035-2
					W/O	W/O	3-1734035-2
					W/	W/O	2-1734035-4
					W/O	W/	2-1734035-3
					W/O	W/O	2-1734035-2
					W/O	W/	1-1734035-3
					W/O	W/O	1-1734035-2
					W/	W/O	1734035-5
					W/	W/O	1734035-4
					W/O	W/	1734035-3
W/O	W/O	1734035-2					
GROSS WEIGHT	NET WEIGHT	PCS/REER	REERS /CARTON	QUANTITY	MYLAR	LONG CARRIER & COVER TAPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				TE Connectivity			
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		MINI USB, R/A, SMT, B TYPE			
				SIZE CAGE CODE DRAWING NO RESTRICTED TO			
				A300779C=1734035			
				CUSTOMER DRAWING			
MATERIAL		FINISH		SCALE		SHEET 4 OF 4	