


REVISIONS					
P	LTR	DESCRIPTION	DATE	DN	APPO
U3		ECR-25-266219	22DEC2025	ABS	PS

- ② .065/.061 DIMENSION MAY GO TO .067 ON POSTS WITH AN A DIMENSION OF 1.187 OR LONGER.
- ③ POINT OF MEASUREMENT FOR PLATING THICKNESS
- ④ .000100-.000200 BRIGHT TIN-LEAD OVER .000030 NICKEL.
- ⑤ .000030 GOLD IN AREA D, GOLD FLASH ON REMAINDER OF POST, ALL OVER .000050 NICKEL.
- ⑥ .000015 GOLD IN AREA D, GOLD FLASH ON REMAINDER OF POST, ALL OVER .000050 NICKEL.
- ⑦ .000050 GOLD OVER .000050 NICKEL OVER ENTIRE POST.
- ⑧ .000015 GOLD IN AREA D, .000100-.000200 BRIGHT TIN-LEAD ON SOLDER AREA, WITH ENTIRE POST UNDERPLATED .000050 NICKEL.
- ⑨ .000030 GOLD IN AREA D, .000100-.000200 BRIGHT TIN-LEAD ON SOLDER AREA, WITH ENTIRE POST UNDERPLATED .000050 NICKEL.
- ⑩ OBSOLETE PART NUMBER.
- ⑪ .000100-.000200 MATTE TIN OVER .000030 NICKEL.
- ⑫ PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- ⑬ ROHS 2002/95/EC COMPLIANT.



FINISH	E	D	C	B	A	LOOSE PIECE PART NO	PART NUMBER
⑩	-	-	.200	.825	.587	-	⑬ 7-85842-0
⑪	-	-	.200	1.430	1.187	-	⑬ 6-85842-1
⑪	-	-	.200	.990	.750	-	⑬ 5-85842-8
⑪	-	-	.200	1.550	1.310	-	⑬ 5-85842-5
⑪	-	-	.200	.645	.405	5-85832-1	⑬ 5-85842-2
⑪	-	-	.200	.837	.587	-	4-85842-6
⑪	-	-	.200	.655	.405	-	4-85842-5
④	-	.950	.500	1.300	1.062	2-86211-3	⑩ 4-85842-4
⑨	.145	1.200	.700	1.550	1.310	2-86211-2	⑩ 4-85842-3
⑨	.145	1.080	.500	1.430	1.187	2-86211-1	⑩ 4-85842-2
⑨	.145	.950	.500	1.300	1.062	2-86211-0	⑩ 4-85842-1
⑨	.145	.765	.400	1.115	.875	1-86211-9	⑩ 4-85842-0
⑨	.145	.640	.300	.990	.750	1-86211-8	⑩ 3-85842-9
⑨	.145	.550	.300	.900	.662	1-86211-7	⑩ 3-85842-8
⑧	.145	.475	.200	.825	.587	1-86211-6	⑩ 3-85842-7
⑧	.145	.475	.200	.825	.587	1-86211-5	⑩ 3-85842-6
⑧	.145	.295	.100	.845	.405	85832-8	⑩ 3-85842-5
⑧	.145	.295	.100	.645	.405	85832-7	⑩ 3-85842-4
⑥	-	1.080	.500	1.430	1.187	1-86211-4	⑩ 3-85842-3
⑥	-	.640	.300	.990	.750	1-86211-3	⑩ 3-85842-2
⑥	-	1.200	.700	1.550	1.310	1-86211-2	3-85842-1
④	-	-	.200	1.115	.875	1-86211-1	⑩ 3-85842-0
⑦	-	.950	.500	1.300	1.062	1-86211-0	⑩ 2-85842-8
⑦	-	-	.200	.645	.405	85832-6	⑩ 2-85842-7
⑥	-	.190	.100	.540	.300	86211-9	⑩ 2-85842-6
④	-	-	.200	.540	.300	86211-8	⑩ 2-85842-4
⑥	-	-	.200	1.550	1.310	85841-4	2-85842-3
⑥	-	.475	.200	.825	.587	86211-7	⑩ 2-85842-2
⑤	-	1.080	.500	1.430	1.187	86211-6	⑩ 2-85842-1
④	-	-	.200	.825	.587	86211-5	2-85842-0
⑥	-	-	.200	.990	.750	85876-3	1-85842-9
⑤	-	.475	.200	.825	.587	86211-4	1-85842-8
⑤	-	.765	.400	1.115	.875	86211-3	1-85842-6
⑥	-	.295	.100	.645	.405	85832-5	1-85842-4
⑤	-	.550	.300	.900	.662	86211-2	⑩ 1-85842-3
④	-	-	.200	1.430	1.187	86211-1	⑩ 1-85842-1
⑤	-	.640	.300	.990	.750	85876-2	85842-9
④	-	-	.200	.990	.750	85876-1	85842-8
⑤	-	1.200	.700	1.550	1.310	85841-2	85842-6
④	-	-	.200	1.550	1.310	85841-1	85842-5
⑤	-	.295	.100	.645	.405	85832-2	85842-3
④	-	-	.200	.645	.405	85832-1	85842-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DATE: 10JUL89
 CHK: KATE HELM
 DATE: 17JUL89

TE Connectivity

APPO: H MOLL
 DATE: 17JUL89
 NAME: CONTACT, MOD 1 MALE, (.031x.062)

PRODUCT SPEC: SAM BEAM

APPLICATION SPEC: -

SIZE: A1
 CAGE CODE: 00779
 DRAWING NO: 85842

WEIGHT: -

CUSTOMER DRAWING

SCALE: 20:1
 SHEET: 1 of 1
 REV: U3