






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PROPOSAL DESIGN	03AUG2018	WY	SZ
	A	REVISED	27JUL2020	WY	SZ

- 1
- "TE", PART NUMBER, AND DATECODE TO BE MARKED IN AREA SHOWN.
PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES.
- 2
- MATERIAL:
HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC,BLACK, UL94 V-O
SIGNAL CONTACT - COPPER ALLOY
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- 3
- CONTACT PLATING: NOBLE METAL PLATING ON CONTACT FUNCTIONAL AREA
OF POWER AND SIGNAL CONTACTS.
- 4
- MECHANICAL CONNECTOR KEEP OUT ZONE.
- 5
- DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6
- PCB - HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- 7
- PCB - .0453±.0010 DRILLED HOLES PLATED WITH .0003 MIN Sn
OVER .001 TO .003 Cu PLATING TO ACHIEVE A .040 ±.003 HOLE.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.25
3 PLC ±0.15
4 PLC ±
ANGLES ±

FINISH



DWN 03AUG2018
WY
CHK 03AUG2018
WY
APVD 03AUG2018
SZ

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

5LP + 24S + 2P
DESCRIPTION

2334570-4
PART NUMBER



TE Connectivity

NAME
RIGHT ANGLE RECEPTACLE, SOLDER
MULTI-BEAM PLUS

SIZE CAGE CODE DRAWING NO

A300779C-2334570-4

RESTRICTED TO

-

SCALE 1:1

SHEET 1 OF 2

REV A

