





P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. PI9153	03JAN2006	-	RDR
	A	REVISED PER E.O. P20618	26OCT2010	-	RDR
	A1	REVISED PER PCN E-20-013840	18SEP2020	MK	IG
	A2	REVISED PER PCN E-20-017587	10MAR2021	CO	IG




PIN



SOC



SOC



PIN

5 DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGITS. (14=2014)
MONTH: THIRD DIGIT, EXCLUDING 1.A=JAN., B=FEB., C=MARCH...(K=OCT.)
DAY: FOURTH AND FIFTH DIGIT (14=14th DAY)
HOUR: SIXTH AND SEVENTH DIGIT (11=11AM)

4. THIS PART MATES WITH HDP24-18-6P/S*-C030. * = TYPE OF SEAL.

3. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DWG. 0425-015-0000 AND 0425-021-0000.


2. THIS CONNECTOR WILL ACCOMMODATE THE FOLLOWING WIRE INSULATION DIAMETERS.

SEAL TYPE	CONTACT SIZE	MIN O.D.	MAX O.D.	3 WIRE GAUGE AWG [mm ²] RANGE
N	4	.280 [7.11]	.292 [7.42]	6 [13]
E	4	.261 [6.63]	.292 [7.42]	6 [13]

1. CONSULT FACTORY FOR ELECTRICAL AND MATERIAL SPECIFICATIONS.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCH [MM]



MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±.025
4 PLC ±
ANGLES ±

FINISH

DWN 08FEB2006

R.MESSENGER

CHK 25OCT2010

R.MESSENGER

APVD 10NOV2010

S.BEARD

PRODUCT SPEC

108-151015

APPLICATION SPEC

114-151015

WEIGHT 43.4 g

CUSTOMER DRAWING



TE Connectivity

NAME
PLUG CONNECTOR 18-6 ARRANGEMENT
HDP20 SERIES -C030 MOD

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-HDP26-18-6PSX-C030 -

SCALE 1.000 SHEET 1 OF 1 REV A2